




Product Item number	SELECT TL5 electrical toilet lifter with tilt function, for wall outlet R9221000
Colour	VVS:617989900 NRF:1617110 EAN:5708590390963 FDA:IKX/D319729 White
Product description	 SELECT toilet lifts are available in several models and colors for both wall outlet and floor outlet. They are available in electrically or manually height-adjustable versions, with or without side profiles and for standard toilet bowls and shower toilets. All developed with a focus on hygiene and easy cleaning. SELECT TL5 toilet lifter with tilt function, for wall outlet. Incl. cistern with dual flushing system preset at 3/6 litres (can be changed to 2/4 litres). Electrically height adjustable 220 mm with control panel on support arm. The tilt function is constrained to the height adjustment. Meaning that the toilet attachment plate will tilt when lifted to upper position and reposition when the unit is lowered. The maximum tilt is 8 degrees. Toilet pan, toilet seat and support arms (required for height adjustment) to be ordered separately. Excl. wall mounting kit.
Adjustability	Height adjustable
Adjustment height	220 mm
Product capacity	Maximum user weight (MUM): 150 kg. Maximum load (SWL): 235 kg. (user weight + accessories). When the toilet lifter is loaded with 235 kg, each wall fastener is loaded with 65 kg. <i>The toilet lifter has been tested statically with 587,5 kg, which is a requirement according to the applied assistive products standards. Please note that most toilet pans compatible with this lifter have been tested up to 400 kg.</i>
Speed upwards	Speed up mm: 7 mm/s Speed down mm: 7 mm/s
Noise level	50 dB



PRESSALIT®

Product	SELECT TL5 electrical toilet lifter with tilt function, for wall outlet
Item number	R9221000
Materials	The toilet lifter is constructed of painted steel, stainless steel and the cover fairing is made of PMMA/ABS plastics.
Ergonomy	The integrated tilt function supports a natural forward movement, making sit-to-stand transitions easier and more secure for users with reduced mobility. By tilting the user into an optimal position, the TL5 improves stability and reduces physical strain during transfers. This enhances both user independence and caregiver working conditions. It is designed for adult users, and can also be used by children under adult supervision.
Features	• Tilt function • Electrically height adjustable • Control panel on support arm • Dual flushing system
Mains connection (V)	230
Actuator (motor)	LA40
Control box	CA63
Power consumption (maximum load)	Power consumption by maximum load, watt: 420 W Power consumption by standby: 0,5 W
Warranty	Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.



Product	SELECT TL5 electrical toilet lifter with tilt function, for wall outlet
Item number	R9221000
Cleaning	The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use corrosive or abrasive cleaners as it may result in the surface being damaged. For surface disinfection, chlorine-based disinfectants may be used according to the product specification and safety precautions for these products. The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container. DISINFECTANTS: Clinimax Difficil-S Erisan OXY+ Sprit (husholdningsprit) Suma Bac D10 Virkon Rodalon Desinfektionsspray Lysoformin Spezial CaviCide Sufanios Premium Tvättssprit 70% NON-DISINFECTANTS: Suma Star free D1 Taski 100 Taski 200 Milizid Citro The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.
WEEE	Please enquire of your local Pressalit subsidiary or distributor (in countries where there is no subsidiary) that will arrange for recycling of electronic waste in accordance with the WEEE directive.



PRESSALIT®

Product	SELECT TL5 electrical toilet lifter with tilt function, for wall outlet
Item number	R9221000

Installation in different wall types

	Concrete >B25 V8605 - Mounting kit, 4 coach screws Ø10 x 70, plugs SX12, with grey screw covers. To be ordered separately.	
	Solid Brick >= Mz12 V8605 - Mounting kit, 4 coach screws Ø10 x 70, plugs SX12, with grey screw covers. To be ordered separately.	
	Solid Sand Lime Brick >= Hlz12 V8605 - Mounting kit, 4 coach screws Ø10 x 70, plugs SX12, with grey screw covers. To be ordered separately.	
	Aerated Concrete P4 V8655 - Mounting kit, 4 coach screws Ø10 x 70, plugs GB14, with grey screw covers. To be ordered separately.	
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood V8605 - Mounting kit, 4 coach screws Ø10 x 70, plugs SX12, with white screw covers. NB! Plugs are not needed. To be ordered separately.	



Product Item number	SELECT TL5 electrical toilet lifter with tilt function, for wall outlet R9221000		
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.		
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (2 mm) Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.		
	Drywall (2 x 12,5 mm) water-resistant Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.		