




# PRESSALIT®

|                                                                |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |
|----------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Product</b><br><b>Item number</b>                           | PLUS shower seat 310, fixed height<br>R7304000                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |
| <b>Colour</b>                                                  | VVS:777513000<br>NRF:6317084<br>EAN:5708590359274<br>HMI: 121181<br>FDA:INN/D135865<br>White                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
| <b>Product description</b>                                     | <div>  </div> <p>PLUS shower seats are offered in a number of colours. They are available as both fixed height, electrically adjustable and manually adjustable, and with an option of back and armrests.</p> <p>They are suitable for wall-mounting or for fitting to Pressalit PLUS wall tracks.</p> <p>PLUS shower seat 310. For fixed mounting. The seat is foldable.</p> <p>Materials: Comfortable polyurethane foam over a plywood core, fitted to an aluminium profile.</p> <p>Excl. mounting kit.</p> <p><i>Replaces R7310</i></p> |
| <b>Adjustability</b><br><b>Product capacity</b>                | Fixed mounting<br><br>Maximum user mass: 200 kg.<br>When the seat is loaded with 200 kg, each wall fastener is loaded with 113 kg. <p><i>The seat has been tested statically with safety factor 1.5, which is a requirement according to the applied assistive products standards.</i></p>                                                                                                                                                                                                                                                                                                                                    |
| <b>Materials</b><br><br><b>Ergonomy</b><br><br><b>Features</b> | <p>The shower seat is made of polyurethane (PU) foam with a plywood core and this is covered with an in-mould coated surface that is protected using a clear PU lacquer. Internal components and fasteners are primarily made of stainless steel. The hinge barrel is capped with ABS.</p> <p>Ergonomically designed seat - contact surface are 450 x 437 mm. Soft and slip-resistant material that has a warm feel.</p> <p>The seat can fold up when not in use or to maximise floor space.</p>                                                                                                                              |
| <b>Warranty</b>                                                | Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |








|                    |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
|--------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Product</b>     | PLUS shower seat 310, fixed height                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |
| <b>Item number</b> | R7304000                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |
| <b>Cleaning</b>    | <p>PLUS shower seat</p> <p>The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p><b>DISINFECTANTS:</b><br/>Erisan OXY+<br/>Tvättsprit 70%<br/>CaviCide surface disinfectant decontaminant cleaner<br/>Rodalon Desinfektionsspray<br/>Terralin protect (SCHÜLKE+)<br/>Dismonzon Plus (BODE Chemie GmbH)</p> <p><b>NON-DISINFECTANTS:</b><br/>Wetrok Caledor (Wetrok)<br/>Petrosol Citro (Büfa)</p> <p>Important: Polyurethane surfaces of PLUS shower seats and PLUS backrests contains an antibacterial surface, which will be compromised if cleaned with anything other than soap and water.</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p> <p><b>DECALCIFICATION OF ALUMINUM PARTS:</b><br/>Pressalit recommends that chalky deposits be removed from wall tracks and other aluminum parts using a solution of three parts 30% acetic acid to seven parts tap water. When the aluminum parts have been washed down with this solution, the parts must be wiped over with a damp cloth wrung out in clear water.</p> |



|                    |                                    |
|--------------------|------------------------------------|
| <b>Product</b>     | PLUS shower seat 310, fixed height |
| <b>Item number</b> | R7304000                           |

## Installation in different wall types

|                                                                                     |                                                                                                                                                                                                                                                                                                 |
|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|    | <p><b>Concrete &gt;B25</b></p> <p>V8604 - Mounting kit, 4 countersunk screws Ø8 x 70, plugs SX10.<br/>To be ordered separately.</p>                                                                          |
|   | <p><b>Solid Brick &gt;= Mz12</b></p> <p>V8604 - Mounting kit, 4 countersunk screws Ø8 x 70, plugs SX10.<br/>To be ordered separately.</p>                                                                   |
|  | <p><b>Solid Sand Lime Brick &gt;= Hlz12</b></p> <p>V8604 - Mounting kit, 4 countersunk screws Ø8 x 70, plugs SX10.<br/>To be ordered separately.</p>                                                       |
|  | <p><b>Aerated Concrete P4</b></p> <p>V8654 - Mounting kit, 4 countersunk bolts M8 x 35, plugs FTP M 8.<br/>To be ordered separately.</p>                                                                   |
|  | <p><b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</b></p> <p>V8604 - Mounting kit, 4 countersunk screws Ø8 x 70, plugs SX10. NB! Plugs are not needed.<br/>To be ordered separately.</p>  |



# PRESSALIT®

|                                      |                                                                                                                                                                                                                           |
|--------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Product</b><br><b>Item number</b> | PLUS shower seat 310, fixed height<br>R7304000                                                                                                                                                                            |
|                                      | <p><b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood</b></p> <p>Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.</p>       |
|                                      | <p><b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (2 mm)</b></p> <p>Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.</p> |
|                                      | <p><b>Drywall (2 x 12,5 mm) water-resistant</b></p> <p>Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.</p>                                                                     |

It is the responsibility of the installer to ensure that suitable wall fasteners are used.

[pressalit.com](http://pressalit.com)

Pressalit A/S  
 Pressalitvej 1  
 DK-8680 Ry  
 Tel.: +45 8788 8788  
 Fax: +45 8788 8789  
 E-mail: [pressalit@pressalit.com](mailto:pressalit@pressalit.com)

# PRESSALIT®