




PRESSALIT®










Product	Wash cabinet for changing tables
Item number	R8791000
Colour	White
Product description	VVS: 777633420 RSK: 7508077 EAN: 5708590395340  Create a smarter everyday life in the kindergarten's toilet and changing room with Pressalit's innovative wash cabinet, which is installed between two changing tables. It makes optimal use of space and provides easy access to washing and storage - exactly where it is needed most. Functional design and durable materials ensure both hygiene and efficiency in a busy everyday life, and make changing time easier for both children and careworkers. Wash cabinet, 820 x 491 mm, wall-mounted, fixed, with under-glued wash basin, 3 wire baskets, drain plug and inlet and outlet hoses. Excl. tap and wall mounting screws. The wash cabinet is delivered assembled.
Adjustability	Fixed mounting
Product capacity	Maximum load 100 kg
Materials	CDF (Compact Density Fiberboard), painted steel, stainless steel
Ergonomy	Easy access to diapers, towels, toys etc. - with 3 x wire baskets. Improved use of the room's m2 by sharing a basin vanity between two changing tables. Flexible position of vanity - right or left to a changing table.
Features	Wall-mounted wash cabinet, raised from the floor and supported only at the front by one leg, ensures easy cleaning of the floor. Side covers prevent the risk of crushing when raising/lowering changing tables. Good storage with 3 pull-out baskets. Incl. glued stainless steel wash basin. Incl. inlet and drain hoses with water trap. Excl. tap. Excl. wall mounting screws.
Warranty	Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.






PRESSALIT®

Product	Wash cabinet for changing tables
Item number	R8791000

Installation in different wall types

	Concrete >B25 V8600 - Mounting kit, 6 coach screws Ø6 x 70 - plugs SX8. To be ordered separately.	
	Solid Brick >= Mz12 V8600 - Mounting kit, 6 coach screws Ø6 x 70 - plugs SX8. To be ordered separately.	
	Solid Sand Lime Brick >= Hlz12 V8600 - Mounting kit, 6 coach screws Ø6 x 70 - plugs SX8. To be ordered separately.	
	Aerated Concrete P4 V8660 - Mounting kit, 8 countersunk bolts M8 x 35, plugs FTP M 8. To be ordered separately.	
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood V8600 - Mounting kit, 6 coach screws Ø6 x 70 - plugs SX8.. NB! Plugs are not needed. To be ordered separately.	



Product Item number	Wash cabinet for changing tables R8791000		
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (2 mm) Wall fasteners (6 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.		
	Drywall (2 x 12,5 mm) water-resistant Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.		