




PRESSALIT®

Product Item number	Pressalit Public Premium Hand dryer with sensor, matte black PX40515
Product description	VVS:776133331 NRF:1438622 RSK:8865105 EAN:5708590395524  Stainless steel warm air hand dryer for wall mounting. Low-noise fan with sensor activated at 172mm (± 20 mm). Drying time approx. 15 sec. Connection for fixed installation or installation via circuit breaker. Permanent installation must be carried out by an authorized electrician Power 840-1000 W. 230 V / 50/60 Hz
Materials	European stainless steel (AISI 304)
Warranty	A 2-year warranty is provided for material and manufacturing defects.
Cleaning	The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.
WEEE	Please enquire of your local Pressalit subsidiary or distributor (in countries where there is no subsidiary) that will arrange for recycling of electronic waste in accordance with the WEEE directive. Subject to changes in the product range, technical changes and printing errors.



PRESSALIT®

Product	Pressalit Public Premium Hand dryer with sensor, matte black
Item number	PX40515

pressalit.com

Pressalit A/S
Pressalitvej 1
DK-8680 Ry
Tel.: +45 8788 8788
Fax: +45 8788 8789
E-mail: pressalit@pressalit.com

PRESSALIT®

8. juli 2026