



PRESSALIT®

Pressalit Trend incl. Pressalit Style D2 1206

Wall hung toilet with circular flush, incl. toilet seat
Toilet seat with soft close, lift-off and antibacterial effect, incl. hinge in stainless steel

Item number




CP1206111CF
VVS: 613326611
NRF: 1579369
RSK: 7822150
EAN: 5708590398631

The Pressalit Trend Combi Pack with the Style D2 toilet seat brings contemporary design and personal expression together in one refined solution. The rimless, wall-hung toilet features the efficient Circular Flush system, ensuring a quiet and splash-free flush while keeping everyday cleaning simple. Paired with the Pressalit Style D2, the pack gains an extra layer of exclusivity. The seat's slim, elegant profile matches the toilet's minimalist lines and adds a light, modern touch to the bathroom. With interchangeable design emblems, it's easy to align the seat with the rest of your Pressalit Style accessories or simply switch colours whenever you want a fresh look. Each pack includes two sets of design emblems, and additional options are available if you want to customise further. The Pressalit Style D2 comes in six carefully selected colours, giving you the freedom to craft the atmosphere you want. Behind the aesthetics is the durability Pressalit is known for, supported by a 10-year warranty and features like Soft Close, Lift-Off, and Pressalit SteadyFix® for added stability. The result is a stylish and hygienic combination that suits modern bathrooms where personalisation, comfort, and quality all matter.



Colour

Black (RAL 9005)





PRESSALIT®

Pressalit Trend incl. Pressalit Style D2 1206

Wall hung toilet with circular flush, incl. toilet seat
seal with soft close, lift-off and antibacterial effect, incl. hinge in stainless steel

Materials

BOWL:
Porcelain

TOILET SEAT:

The material is colour ingrained duroplast (UF A 10 = urea formaldehyde) that contains no environmentally hazardous substances. UF plastic comprises approx. 70% urea formaldehyde resin, 30% cellulose, as well as 5% minerals, pigments, lubricants and moisture content. Free formaldehyde is released during the production process. Pressalit toilet seats have been measured after curing ($< 0.01 \text{ mg/m}^3$) to emit significantly below the permitted EU limit of 0.08 mg/m^3 .

ANTIBACTERIAL:

This toilet seat features an antibacterial additive with biocidal silver phosphate glass, which helps prevent bacterial growth.

BUFFERS:

EVA (copolymer made of ethylene and vinyl acetate).

DAMPER KIT:

Hydraulic damper with damper housing in stainless steel or thermoplastic, mounted with plastic parts in thermoplastic.

MOUNT/HINGES:

Stainless steel and thermoplastic.

Product capacity

Load - ring seat 240 kg

Weight

31,055 kg

Carton size

540x410x510 mm

Gross weight

33,725 kg

Weight per crate

33,725 kg

Qty per crate

1

Crates per pallet

5

Qty per pallet

5



PRESSALIT®

Pressalit Trend incl. Pressalit Style D2 1206

**Wall hung toilet with circular flush, incl. toilet seat

Toilet seat with soft close, lift-off and antibacterial effect, incl. hinge in stainless steel**

Warranty

Pressalit provides a 10-year warranty on toilet seats and a 5-year warranty on toilet bowls against presentation of a valid receipt. In the event of a complaint, please contact the retailer or store where the product was purchased. The warranty covers defective materials and/or manufacturing defects and/or functional limitations that may occur following proper use and cleaning of the product. Pressalit reserves the right to examine the product at our factory. In the case of a valid complaint, Pressalit will either:
- supply spare parts, or
- replace the product with an identical or a similar model.
If the color of the toilet seat is no longer available, Pressalit reserves the right to supply a similar model in white. Upon replacement or delivery of spare parts, the warranty period will not be extended nor renewed. If replacement is not possible, Pressalit is entitled instead to refund the purchase price.

Subject to changes in the product range, technical changes and printing errors.

pressalit.com

PRESSALIT®