



PRESSALIT®

Product Item number	Pressalit Public Premium Infrared sensor module for dispensers PX00799
Product description	<p>VVS:774565999 NRF:1438623 RSK:8920357 EAN:5708590392066</p> <p>Infrared sensor with pump for use in soap dispensers. The sensor reacts to light differences. Detection distance approx. 5 cm.</p> <p>Fits soap dispensers PX10320, PX30320, PX40320, PY10715, PY20725 and PY30735. 3V. Requires 2 LR14 batteries (not included).</p>
Warranty Cleaning	<p>A 2-year warranty is provided for material and manufacturing defects.</p> <p>The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.</p> <p>Subject to changes in the product range, technical changes and printing errors.</p>

pressalit.com