



|                            |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |
|----------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Product</b>             | PLUS fitting with strap                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
| <b>Item number</b>         | RT360035                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
| <b>Colour</b>              | <p>VVS: 777569605<br/>EAN: 5708590146737<br/>NBS: N13:436</p> <p>Red (RAL 3003)</p>                                                                                                                                                                                                                                                                                                                                                                                                                                   |
| <b>Product description</b> | <p>PLUS hand rail wall mounting with strap.<br/>For assembling tubes with diameter 33 mm.<br/>Requires other hand rail elements for installation.<br/><i>Please enquire for special hand rail solutions.</i><br/>Excl. mounting kit.<br/>See Technical datasheet (pdf) for information on fixings suitable for various wall types.</p> <p>PLUS hand rail wall mounting with strap.<br/>For assembling tubes with diameter 33 mm.<br/>Requires other hand rail elements for installation.<br/><i>Please enquire for special hand rail solutions.</i><br/>Materials: Plastics.<br/>Excl. mounting kit.</p> |
| <b>Product capacity</b>    | <p>Maximum load: With a span up to 1000 mm: 210 kg<br/>With a span up to 1300 mm: 150 kg.</p>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |
| <b>Materials</b>           | <p>Cover cap: Cyclopy plastic</p> <p>Strap: Nylon (PA)</p>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |
| <b>Warranty</b>            | Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |
| <b>Cleaning</b>            | The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.                                                                                                                                                                                                                                                                                                                                                                                                                               |



PRESSALIT®

|                    |                         |
|--------------------|-------------------------|
| <b>Product</b>     | PLUS fitting with strap |
| <b>Item number</b> | RT360035                |

## Installation in different wall types

|                                                                                     |                                                                                                                                                                                |                                                                                       |
|-------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
|    | <b>Concrete &gt;B25</b><br>V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.                                                     |    |
|   | <b>Solid Brick &gt;= Mz12</b><br>V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.                                               |   |
|  | <b>Solid Sand Lime Brick &gt;= Hlz12</b><br>V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.                                    |  |
|  | <b>Aerated Concrete P4</b><br>V8665 - Mounting kit, 4 bolts M5 x 50 - plugs FTP K 6. To be ordered separately.                                                                 |  |
|  | <b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</b><br>V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8. NB! Plugs are not needed. To be ordered separately. |  |



# PRESSALIT®

| Product<br>Item number                                                              | PLUS fitting with strap<br>RT360035                                                                                                                                                                            |                                                                                       |                                                                                     |
|-------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
|    | <b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood</b><br>Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.       |    |  |
|    | <b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (2 mm)</b><br>Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar. |    |  |
|  | <b>Drywall (2 x 12,5 mm) water-resistant</b><br>Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.                                                                     |  |                                                                                     |

[pressalit.com](http://pressalit.com)