



# PRESSALIT®

|                                      |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
|--------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Product</b><br><b>Item number</b> | PLUS handrail section 652 mm, incl. wall rosette and strap<br>RT331035                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |
| <b>Colour</b>                        | VVS:777569315<br>EAN:5708590146621<br>NBS:N13:436<br><br>Red (RAL 3003)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |
| <b>Product description</b>           | <div>  </div> <p>PLUS hand rail tube, with wall rosette and strop.<br/> Length 652 mm, diameter 33 mm.<br/> Requires other hand rail elements for installation.<br/> <i>Please enquire for special hand rail solutions.</i><br/> Excl. mounting kit.<br/> See Technical datasheet (pdf) for information on fixings suitable for various wall types.</p> <p>PLUS hand rail tube, with wall rosette and strop.<br/> Length 652 mm, diameter 33 mm.<br/> Requires other hand rail elements for installation.<br/> <i>Please enquire for special hand rail solutions.</i><br/> Materials: Powder-coated aluminium and plastics.<br/> Excl. mounting kit.</p> |
| <b>Product capacity</b>              | Maximum load: With a span up to 1000 mm: 210 kg<br>With a span up to 1300 mm: 150 kg.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |
| <b>Materials</b>                     | Basic material: Aluminium<br><br>Surface material: Polyester lacquer<br><br>Cover cap: Cyclopy plastic<br><br>Strap: Nylon (PA)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
| <b>Ergonomy</b>                      | The 33 mm diameter enables the rail to be held comfortably and firmly. The projection of 50 mm from the wall makes it easy to take hold of the rail.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| <b>Warranty</b>                      | Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |



# PRESSALIT<sup>®</sup>

|                    |                                                                                                                                                                            |
|--------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Product</b>     | PLUS handrail section 652 mm, incl. wall rosette and strap                                                                                                                 |
| <b>Item number</b> | RT331035                                                                                                                                                                   |
| <b>Cleaning</b>    | The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged. |



PRESSALIT®

|                    |                                                            |
|--------------------|------------------------------------------------------------|
| <b>Product</b>     | PLUS handrail section 652 mm, incl. wall rosette and strap |
| <b>Item number</b> | RT331035                                                   |

## Installation in different wall types

|                                                                                     |                                                                                                                                                                                |                                                                                       |
|-------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
|    | <b>Concrete &gt;B25</b><br>V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.                                                     |    |
|   | <b>Solid Brick &gt;= Mz12</b><br>V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.                                               |   |
|  | <b>Solid Sand Lime Brick &gt;= Hlz12</b><br>V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.                                    |  |
|  | <b>Aerated Concrete P4</b><br>V8665 - Mounting kit, 4 bolts M5 x 50 - plugs FTP K 6. To be ordered separately.                                                                 |  |
|  | <b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</b><br>V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8. NB! Plugs are not needed. To be ordered separately. |  |



# PRESSALIT®

| Product<br>Item number                                                              | PLUS handrail section 652 mm, incl. wall rosette and strap<br>RT331035                                                                                                                                         |                                                                                       |                                                                                     |
|-------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
|    | <b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood</b><br>Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.       |    |  |
|    | <b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (2 mm)</b><br>Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar. |    |  |
|  | <b>Drywall (2 x 12,5 mm) water-resistant</b><br>Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.                                                                     |  |                                                                                     |

pressalit.com

Pressalit A/S  
 Pressalitvej 1  
 DK-8680 Ry  
 Tel.: +45 8788 8788  
 Fax: +45 8788 8789  
 E-mail: [pressalit@pressalit.com](mailto:pressalit@pressalit.com)

# PRESSALIT®