




Product Item number	PLUS sink bracket with lever control, manually height adjustable with pneumatic cylinder R4650
Product description	VVS: 654002100 NRF: 6132532 RSK: 7972590 EAN: 5708590309439 HMI: 71762 NBS: N13:30,335 FDA: ILW/D142473  PLUS sink brackets are available in electrically, pneumatically and manually height adjustable versions. They are suitable for wall-mounting or for fitting to Pressalit PLUS wall tracks. PLUS sink bracket, pneumatic-assisted. The lever control is placed at the front of the sink. The lever control can also be used as a towel bar and can be placed on either side of the sink. Manually height adjustable by 11.8" (stepless). Recommendation: Flexible feed and waste system R2085/R2087. Materials: Aluminium and ABS polymer. Incl. fixing bolts for sink. Excl. mounting kit.
Adjustability Adjustment height Product capacity	Height adjustable 11,82 inch Maximum load: 298 lbs. Suitable for sinks weighing no more than 49 lbs. When the sink is loaded with 298 lbs, each wall fastener will be carrying 126 lbs. <i>Sink brackets need to be able to carry the weight of the sink, as well as support the weight of the person who is leaning against the sink or who is using the sink to rise from seated position.</i> Neither sink nor sink bracket are intended to carry the full body weight of a person, and the test methods applicable to sink brackets reflect this: ISO 17966 prescribes a static test on the front edge of the sink at 75% of maximum user weight, i.e. when the maximum load on a sink bracket is given as 298 lbs and the wash basin weighs 49 lbs, it is – according to ISO 17966 – the equivalent of a user weighing 332 lbs leaning on the front edge of the wash basin.



PRESSALIT®

Product	PLUS sink bracket with lever control, manually height adjustable with pneumatic cylinder
Item number	R4650
Materials	The sink bracket is primarily made of 3/8" anodized aluminium. The ends of the bracket cover are capped with ABS polymer. The bracket is available with a lever control consisting of an ABS polymer switch at the end of an anodized aluminium arm
Ergonomy	The height of the sink is easily adjusted the lever control. The sink bracket is compatible with all types of bolt-mounted sink. It's rounded, sleek design makes it easy to clean thoroughly.
Features	The arm that holds the lever control can function as a towel bar. The lever control can be placed on the right- or left-hand side of the sink. This sink bracket is supplied as standard with a pneumatic cylinder for sinks weighing 35.3-48.5 lbs, however, it is possible to order it for sinks weighing 17.6-26.5 lbs or 26.5-35.3 lbs.
Warranty	Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.



PRESSALIT®

Product	PLUS sink bracket with lever control, manually height adjustable with pneumatic cylinder
Item number	R4650
Cleaning	This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged. The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container. DISINFECTANTS: Clinimax Difficil-S Erisan OXY+ Sprit (husholdningssprit) Suma Bac D10 Virkon Rodalon Desinfektionsspray Lysoformin Spezial CaviCide Sufanios Premium Tvättsprit 70% NON-DISINFECTANTS: Suma Star free D1 Taski 100 Taski 200 Milizid Citro The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate. DECALCIFICATION OF ALUMINUM PARTS: Pressalit recommends that water deposits (Calcium, lime etc.) be removed from wall tracks and other aluminum parts using a solution of three parts of 30% acetic acid to seven parts tap water. When the aluminum parts have been washed down with this solution, the parts should be wiped over with a damp cloth wrung out in plain water.



PRESSALIT®

Product	PLUS sink bracket with lever control, manually height adjustable with pneumatic cylinder
Item number	R4650

pressalit.com

Pressalit A/S
Pressalitvej 1
DK-8680 Ry
Tel.: +45 8788 8788
Fax: +45 8788 8789
E-mail: pressalit@pressalit.com

PRESSALIT®