



|                                      |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |
|--------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Product</b><br><b>Item number</b> | PLUS fitting with strap and joint<br>RT361108                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| <b>Color</b>                         | VVS:777569618<br>EAN:5708590153889<br>NBS:N13:436<br><br>Dark blue (RAL 5011)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| <b>Product description</b>           | <p>PLUS grab bar wall mounting with strap and tube connector, male and female joint.<br/>For assembling tubes with diameter 1.3".<br/>Requires other grab bar elements for installation.<br/><i>Please enquire for special grab bar solutions.</i><br/>Excl. mounting kit.<br/>See Technical datasheet (pdf) for information on fixings suitable for various wall types.</p> <p>PLUS grab bar wall mounting with strap and tube connector, male and female joint.<br/>For assembling tubes with diameter 1.3".<br/>Requires other grab bar elements for installation.<br/><i>Please enquire for special grab bar solutions.</i><br/>Materials: Plastics.<br/>Excl. mounting kit.</p> |
| <b>Product capacity</b>              | Maximum load: With a span up to 39.4" : 460 lbs.<br>With a span up to 51.2" : 330 lbs.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |
| <b>Materials</b>                     | Cover cap: Cyclopy plastic<br>Strap: Nylon (PA)<br>Connecting unit: Polyphenylene oxide (PPO)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| <b>Warranty</b>                      | Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| <b>Cleaning</b>                      | This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |



PRESSALIT®

|                    |                                   |
|--------------------|-----------------------------------|
| <b>Product</b>     | PLUS fitting with strap and joint |
| <b>Item number</b> | RT361108                          |

## Mounting in different wall types

|                                                                                     |                                                                                                                                                                                                  |                                                                                       |
|-------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
|    | <p><b>Concrete &gt;B25</b></p> <p>V8615 - Mounting kit, 4 bolts Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p>                                                             |    |
|   | <p><b>Solid Brick &gt;= Mz12</b></p> <p>V8615 - Mounting kit, 4 bolts Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p>                                                       |   |
|  | <p><b>Solid Sand Lime Brick &gt;= Hlz12</b></p> <p>V8615 - Mounting kit, 4 bolts Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p>                                            |  |
|  | <p><b>Aerated Concrete P4</b></p> <p>V8665 - Mounting kit, 4 bolts M5 x 50 - plugs FTP K 6, for aerated concrete. To be ordered separately.</p>                                                  |  |
|  | <p><b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</b></p> <p>V8615 - Mounting kit, 4 bolts Ø5 x 50 - plugs SX8. NB!<br/>Plugs are not needed.<br/>To be ordered separately.</p> |  |



| Product<br>Item number                                                              | PLUS fitting with strap and joint<br>RT361108                                                                                                                                                                              |                                                                                       |                                                                                     |
|-------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
|    | <b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood</b><br>Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or WingIt anchors or similar.           |    |  |
|    | <b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (.08 inch)</b><br>Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or WingIt anchors or similar. |    |  |
|  | <b>Drywall (2 x 12,5 mm) water-resistant</b><br>Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.                                                                                 |  |                                                                                     |