



# PRESSALIT®

|                                      |                                                                                                                                                                                                                                                                                                                                               |
|--------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Product</b><br><b>Item number</b> | Pressalit Public Premium Power supply, C 3 volt, suitable for dispensers with infrared sensor<br>PX00789                                                                                                                                                                                                                                      |
| <b>Product description</b>           | VVS: 774565989<br>NRF: 1438637<br>RSK: 8920356<br>EAN: 5708590392059<br><br>Power supply for infrared sensor module. Can be used as a regular power supply from a wall outlet with the module instead of batteries.<br><br>Cable length 1.35 m. Primary: 100V-240V~, 50/60 Hz, 0.5A. Secondary: 3V=, 2A.                                      |
| <b>Warranty</b><br><b>Cleaning</b>   | A 2-year warranty is provided for material and manufacturing defects.<br><br>This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.<br><br>Subject to changes in the product range, technical changes and printing errors. |

[pressalit.com](http://pressalit.com)