




|                            |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |
|----------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Product</b>             | PLUS handrail corner 762 x 762 mm                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |
| <b>Item number</b>         | RT126108                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |
|                            | <p>VVS:777568308</p> <p>NRF:6317184</p> <p>EAN:5708590154053</p> <p>HMI: 25426</p> <p>NBS:N13:436</p> <p>FDA:ILS/D135866</p>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
| <b>Colour</b>              | Dark blue (RAL 5011)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |
| <b>Product description</b> | <p>PLUS handrails are high-quality products and they can be combined in countless ways and they provide the final touch to furnishing a functional and flexible bathroom. A reliable solution with many different options, which can easily lay the grounds for increased independence.</p> <p>PLUS handrail, corner, 33 mm, reversible right/left A: 762 mm x B: 762 mm, for fixed mounting.</p> <p>The projection of 50 mm from the wall makes it easy to take hold of the rail.</p> <p>Inkl. wall rosette, which covers the fixings.</p> <p>Material: Powder-coated aluminium and plastic.</p> <p>Excl. mounting kit.</p> |
| <b>Product capacity</b>    | <p>Maximum load: 235 kg.</p> <p>When the handrail is loaded with 235 kg, each wall fastener is loaded with 56 kg.</p> <p><i>Handrails are tested with a 1.5 safety factor in accordance with the requirements in ISO 17966:2016.</i></p>                                                                                                                                                                                                                                                                                                                                                                                     |
| <b>Materials</b>           | <p>Basic material: Aluminium</p> <p>Surface material: Polyester lacquer</p> <p>Cover cap: Cyclopy plastic</p> <p>Strap: Nylon (PA)</p>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |
| <b>Ergonomy</b>            | <p>The 33 mm diameter enables the rail to be held comfortably and firmly. The projection of 50 mm from the wall makes it easy to take hold of the rail.</p>                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
| <b>Warranty</b>            | <p>Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.</p>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |





# PRESSALIT®

|                    |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
|--------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Product</b>     | PLUS handrail corner 762 x 762 mm                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |
| <b>Item number</b> | RT126108                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| <b>Cleaning</b>    | <p>Handrails ALU</p> <p>The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p><b>DISINFECTANTS:</b></p> <p>Clinimax Difficil-S<br/>Erisan OXY+<br/>Sprit (husholdningsprit)<br/>Suma Bac D10<br/>Virkon<br/>Rodalon Desinfektionsspray<br/>Lysoformin Spezial<br/>CaviCide<br/>Sufanios Premium<br/>Tvättsprit 70%</p> <p><b>NON-DISINFECTANTS:</b></p> <p>Suma Star free D1<br/>Taski 100<br/>Taski 200<br/>Milizid Citro</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p> <p><b>DECALCIFICATION OF ALUMINUM PARTS:</b></p> <p>Pressalit recommends that chalky deposits be removed from wall tracks and other aluminum parts using a solution of three parts 30% acetic acid to seven parts tap water. When the aluminum parts have been washed down with this solution, the parts must be wiped over with a damp cloth wrung out in clear water.</p> |








PRESSALIT®

|                    |                                   |
|--------------------|-----------------------------------|
| <b>Product</b>     | PLUS handrail corner 762 x 762 mm |
| <b>Item number</b> | RT126108                          |

## Installation in different wall types

|                                                                                     |                                                                                                                                                                                                                                                                             |
|-------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|    | <b>Concrete &gt;B25</b><br>V8617 - Mounting kit, 12 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.                                                              |
|   | <b>Solid Brick &gt;= Mz12</b><br>V8617 - Mounting kit, 12 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.                                                        |
|  | <b>Solid Sand Lime Brick &gt;= Hlz12</b><br>V8617 - Mounting kit, 12 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.                                           |
|  | <b>Aerated Concrete P4</b><br>V8667 - Mounting kit, 12 bolts M5 x 50 - plugs FTP K 6.<br>To be ordered separately.                                                                     |
|  | <b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</b><br>V8617 - Mounting kit, 12 screws Ø5 x 50 - plugs SX8. NB!<br>Plugs are not needed.<br>To be ordered separately.  |



| Product<br>Item number                                                              | PLUS handrail corner 762 x 762 mm<br>RT126108                                                                                                                                                                   |                                                                                                                                                                                                                                                             |  |
|-------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|
|    | <b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood</b><br>Wall fasteners (12 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.       |    |  |
|    | <b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (2 mm)</b><br>Wall fasteners (12 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar. |    |  |
|  | <b>Drywall (2 x 12,5 mm) water-resistant</b><br>Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.                                                                      |                                                                                                                                                                        |  |