




# PRESSALIT®

<b>Product</b> <b>Item number</b>	Touchless wash basin mixer tap RT631
<b>Product description</b>	<p>           VVS: 704388104            NRF: 6132551            EAN: 5708590297354            HMI: 123754            NBS: N13:30,335         </p>  <p>           Touchless wash basin mixer tap with scalding protection.            WRAS-approved.         </p>
<b>Features</b>	Temperature adjustment. Battery-operated 6 V. Flow controller (5 l/min.) Infrared sensor technology Protection against scalding
<b>Warranty</b>	Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.
<b>Cleaning</b>	The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.
<b>WEEE</b>	Please enquire of your local Pressalit subsidiary or distributor (in countries where there is no subsidiary) that will arrange for recycling of electronic waste in accordance with the WEEE directive.



# PRESSALIT®

<b>Product</b>	Touchless wash basin mixer tap
<b>Item number</b>	RT631

---

[pressalit.com](http://pressalit.com)

---

Pressalit A/S  
Pressalitvej 1  
DK-8680 Ry  
Tel.: +45 8788 8788  
Fax: +45 8788 8789  
E-mail: [pressalit@pressalit.com](mailto:pressalit@pressalit.com)

# PRESSALIT®