




<p>Product</p> <p>Item number</p>	<p>PLUS 90° angle handrail 400 x 475 mm</p> <p>RT115035</p>
<p>Colour</p> <p>Product description</p>	<p>VVS:777567135</p> <p>NRF:6317174</p> <p>EAN:5708590146287</p> <p>HMI: 25432</p> <p>NBS:N13:436</p> <p>Red (RAL 3003)</p>  <p>PLUS handrails are high-quality products and they can be combined in countless ways and they provide the final touch to furnishing a functional and flexible bathroom. A reliable solution with many different options, which can easily lay the grounds for increased independence.</p> <p>PLUS handrail, angle 90° - left, diameter 33 mm, A: 400 mm x B: 475 mm, for fixed mounting.</p> <p>The projection of 50 mm from the wall makes it easy to take hold of the rail.</p> <p>Inkl. wall rosette, which covers the fixings.</p> <p>Material: Powder-coated aluminium and plastic.</p> <p>Excl. mounting kit.</p>
<p>Product capacity</p>	<p>Maximum load: 235 kg.</p> <p>When the handrail is loaded with 235 kg, each wall fastener is loaded with 56 kg.</p> <p><i>Handrails are tested with a 1.5 safety factor in accordance with the requirements in ISO 17966:2016.</i></p>
<p>Materials</p> <p>Ergonomy</p>	<p>Basic material: Aluminium</p> <p>Surface material: Polyester lacquer</p> <p>Cover cap: Cycoloy plastic</p> <p>Strap: Nylon (PA)</p> <p>The 33 mm diameter enables the rail to be held comfortably and firmly. The projection of 50 mm from the wall makes it easy to take hold of the rail.</p>
<p>Warranty</p>	<p>Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.</p>













Product	PLUS 90° angle handrail 400 x 475 mm
Item number	RT115035
Cleaning	<p>Handrails ALU The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p>DISINFECTANTS: Clinimax Difficil-S Erisan OXY+ Sprit (husholdningsprit) Suma Bac D10 Virkon Rodalon Desinfektionsspray Lysoformin Spezial CaviCide Sufanios Premium Tvättsprit 70%</p> <p>NON-DISINFECTANTS: Suma Star free D1 Taski 100 Taski 200 Milizid Citro</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p> <p>DECALCIFICATION OF ALUMINUM PARTS: Pressalit recommends that chalky deposits be removed from wall tracks and other aluminum parts using a solution of three parts 30% acetic acid to seven parts tap water. When the aluminum parts have been washed down with this solution, the parts must be wiped over with a damp cloth wrung out in clear water.</p>
Declaration of conformity	<p>CE UK MDR This product is in compliance with all relevant requirements of: - Regulation (EU) 2017/745 on medical devices. For the UK: - Medical Device Regulation (MDR) 2002 on medical devices.</p>








Product	PLUS 90° angle handrail 400 x 475 mm
Item number	RT115035

Installation in different wall types

	Concrete >B25 V8617 - Mounting kit, 12 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.	
	Solid Brick >= Mz12 V8617 - Mounting kit, 12 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.	
	Solid Sand Lime Brick >= Hlz12 V8617 - Mounting kit, 12 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.	
	Aerated Concrete P4 V8667 - Mounting kit, 12 bolts M5 x 50 - plugs FTP K 6. To be ordered separately.	
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood V8617 - Mounting kit, 12 screws Ø5 x 50 - plugs SX8. NB! Plugs are not needed. To be ordered separately.	



Product Item number	PLUS 90° angle handrail 400 x 475 mm RT115035
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood Wall fasteners (12 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar. 
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (2 mm) Wall fasteners (12 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar. 
	Drywall (2 x 12,5 mm) water-resistant Mounting in this wall type is not recommended - risk of fatal injury to persons and walls. 