




PRESSALIT®

Product Item number	Changing table, 800 x 900 mm, electrically height adjustable, foldable R8671000
Colour	VVS:777636110 NRF:7501977 RSK:8565113 EAN:5708590338385 HMI: 48572 White
Product description	 Pressalit offers a wide range of daycare changing tables, both free-standing and wall-hung, in several sizes and models. The wall-hung tables are also available in versions where the worktop folds away, which are suitable for rooms with limited space. Of particular use to daycare facilities and kindergartens are the low start wall-hung changing tables, which can be lowered to a height that allows children to climb onto the worktop themselves. All types of daycare changing tables are available in versions with sanitary appliances and a choice of taps, with or without pull-out shower heads. Low start, wallhung, foldable changing table, 800 x 900 mm. With electric motor and transformer, height adjustable from 300 mm - 1000 mm, with wired hand control. Materials: Molded worktop in ABS plastics, synthetic acrylic and powder-lacquered steel. Excl. mounting kit.
Adjustability Adjustment height Product capacity Speed upwards Noise level	Height adjustable 700 mm Max load: 75 kg. Speed up mm: 38 mm/s Speed down mm: 38 mm/s 48 dB
Materials	Lifting unit: Powder-laquered steel. Worktop: ABS with acrylic.



PRESSALIT®

Product Item number	Changing table, 800 x 900 mm, electrically height adjustable, foldable R8671000
Ergonomy Features Mains connection (V) Actuator (motor) Control box Wired remote control Power consumption (maximum load)	The smooth height adjustment ensures that it is always possible to set the table at an ergonomically correct height. The table descends to a very low position, which offers the advantage that toddlers can easily climb up and down themselves. Thereby unnecessary lifting is avoided. Easy-to-clean surfaces ensure optimum hygiene. The integrated gas cylinder enables the table to be folded easily against the wall when not in use to maximise floor space. Integrated safety system prevents entrapment. 230 LA31 Deskline (Linak), 2500N, IPX1 CBD6 (Linak), IP20 HB30 (Linak), IPX4 Power consumption by maximum load, watt: 96 W Power consumption by standby: 0,1 W
Warranty	Pressalit makes a commitment to remedy material and manufacturing defects for a period of three years from the invoicing date.



PRESSALIT®










Product	Changing table, 800 x 900 mm, electrically height adjustable, foldable
Item number	R8671000
Cleaning	The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged. The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container. DISINFECTANTS: Clinimax Difficil-S Erisan OXY+ Sprit (husholdningssprit) Suma Bac D10 Virkon Rodalon Desinfektionsspray Lysoformin Spezial CaviCide Sufanios Premium Tvättsprit 70% NON-DISINFECTANTS: Suma Star free D1 Taski 100 Taski 200 Milizid Citro The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.
WEEE	Please enquire of your local Pressalit subsidiary or distributor (in countries where there is no subsidiary) that will arrange for recycling of electronic waste in accordance with the WEEE directive.



PRESSALIT®

Product	Changing table, 800 x 900 mm, electrically height adjustable, foldable
Item number	R8671000

Installation in different wall types

	Concrete >B25 V8608 - Mounting kit, 6 coach screws Ø10 x 70 - plugs SX12. To be ordered separately.	
	Solid Brick >= Mz12 V8608 - Mounting kit, 6 coach screws Ø10 x 70 - plugs SX12. To be ordered separately.	
	Solid Sand Lime Brick >= Hlz12 V8608 - Mounting kit, 6 coach screws Ø10 x 70 - plugs SX12. To be ordered separately.	
	Aerated Concrete P4 V8658 - Mounting kit, 6 coach screws Ø10 x 70 - plugs GB14. To be ordered separately.	
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood V8608 - Mounting kit, 6 coach screws Ø10 x 70 - plugs SX12. NB! Plugs are not needed. To be ordered separately.	



Product Item number	Changing table, 800 x 900 mm, electrically height adjustable, foldable R8671000
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood Wall fasteners (6 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (2 mm) Wall fasteners (6 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.
	Drywall (2 x 12,5 mm) water-resistant Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.