



# PRESSALIT®

|                                      |                                                                                                                                                                                                                                                                                                                                                |
|--------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Product</b><br><b>Item number</b> | Pressalit Public Premium Infrared sensor module for dispensers<br>PX00799                                                                                                                                                                                                                                                                      |
| <b>Product description</b>           | VVS:774565999<br>NRF:1438623<br>RSK:8920357<br>EAN:5708590392066<br><br>Infrared sensor with pump for use in soap dispensers. The sensor reacts to light differences. Detection distance approx. 5 cm.<br><br>Fits soap dispensers PX10320, PX30320, PX40320, PY10715, PY20725 and PY30735.<br>3V. Requires 2 LR14 batteries (not included).   |
| <b>Warranty</b><br><b>Cleaning</b>   | A 2-year warranty is provided for material and manufacturing defects.<br><br>The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.<br><br>Subject to changes in the product range, technical changes and printing errors. |

[pressalit.com](http://pressalit.com)