




# PRESSALIT®

|                                                                             |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |
|-----------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Product</b><br><b>Item number</b>                                        | Pressalit wall bin 1090<br>1090000                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |
| <b>Colour</b><br><br><br><br><br><br><br><br><br><b>Product description</b> | <p>VVS:777741000<br/>NRF:7000127<br/>EAN:5708590377599<br/>DB: 2279059</p> <p>White</p>  <p>Pressalit wall bin. This easy-to-clean solution features soft, round contours, takes up no floor space and can be operated with just one hand. The inner waste basket is made of recycled plastic and can be used with all types of plastic bags or even without a bag. Experience an exclusive, soft and quiet opening of the wall bin, which stays open until you are finished using it. The magnetic closing function ensures the wall bin stays completely closed.</p> <p>Waste Capacity is 2,5 L.</p> <p>Pressalit wall bin. It features an inner, recycled-plastic waste basket with rounded corners making it easy to clean. The wall bin is suitable for moist waste and can be used with or without a plastic bag. The urea tempered-plastic front has a Soft Open function and a detachable front and inner waste basket to facilitate easier cleaning.</p> |
| <b>Materials</b>                                                            | <p><b>WALL BIN:</b><br/>The material is colour ingrained duroplast (UF A 10 = urea formaldehyde). UF plastic comprises 67% urea formaldehyde resin, 28% cellulose, as well as 5% minerals, pigments, lubricants and moisture content. The raw material from the supplier contains up to 0.03% free formaldehyde and even less following curing.</p> <p><b>ANTIBACTERIAL:</b><br/>This wall bin features an antibacterial additive with biocidal silver chloride, which helps prevent bacterial growth.</p> <p>Wall mount PA6 30% GF. Polyamide. (Glass-fibre reinforced nylon)<br/>Suspension brackets PET/PBT 50% GF. Polyethylene terephthalate/Polybutylene terephthalate. (Glass-fibre reinforced thermoplastic polyester)<br/>Inner basket ABS (Acrylonitrile-butadiene-styrene).</p>                                                                                                                                                                                                                                                           |



# PRESSALIT®

|                    |                                                                                                                                                                                                                                                                                                                                                                                                  |
|--------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Product</b>     | Pressalit wall bin 1090                                                                                                                                                                                                                                                                                                                                                                          |
| <b>Item number</b> | 1090000                                                                                                                                                                                                                                                                                                                                                                                          |
| <b>Warranty</b>    | Pressalit provides a 10-year product warranty on your product. Pressalit will repair or exchange the product for the same or another useable model, at Pressalit's discretion, in the event of a material or manufacturing defect in your product appearing within 10 years of the date of purchase with normal use. This product warranty is conditional upon proof of purchase of the product. |
| <b>Cleaning</b>    | <p>The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.</p> <p>Subject to changes in the product range, technical changes and printing errors.</p>                                                                                                                         |

[pressalit.com](http://pressalit.com)