



# PRESSALIT®

<b>Product</b> <b>Item number</b>	Touchless wash basin mixer tap RT631
<b>Product description</b>	<p>VVS: 704388104 NRF: 6132551 EAN: 5708590297354 HMI: 123754 NBS: N13:30,335</p> <p>Touchless wash basin mixer tap with scalding protection. WRAS-approved.</p>
<b>Features</b>	<p>Temperature adjustment. Battery-operated 6 V. Flow controller (5 l/min.) Infrared sensor technology Protection against scalding</p>
<b>Warranty</b>	Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.
<b>Cleaning</b>	The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.

[pressalit.com](http://pressalit.com)