




PRESSALIT®

Product Item number	Changing table, 800 x 1400 mm, electrically height adjustable, with sanitary appliances and standard mixer tap R8684000
Colour	VVS: 777636320 NRF: 7501983 EAN: 5708590338439 HMI: 100178 White
Product description	 <p>Pressalit offers a wide range of daycare changing tables, both free-standing and wall-hung, in several sizes and models. The wall-hung tables are also available in versions where the worktop folds away, which are suitable for rooms with limited space. Of particular use to daycare facilities and kindergartens are the low start wall-hung changing tables, which can be lowered to a height that allows children to climb onto the worktop themselves.</p> <p>All types of daycare changing tables are available in versions with sanitary appliances and a choice of taps, with or without pull-out shower heads.</p> <p>Low start, wallhung changing table, with sanitary appliances, 800 x 1400 mm. With electric motor and transformer, height adjustable from 300 mm - 1000 mm, with wired hand control and safety stop function. Molded worktop with integrated sink, incl. lever operated mixer tap, feed/waste system and 2 wire baskets. Materials: ABS plastics, synthetic acrylic and powder-lacquered steel. Excl. mounting kit.</p>
Adjustability	Height adjustable
Adjustment height	700 mm
Product capacity	Max load: 75 kg.
Speed upwards	Speed up mm: 38 mm/s Speed down mm: 38 mm/s
Noise level	48 dB



PRESSALIT®

Product	Changing table, 800 x 1400 mm, electrically height adjustable, with sanitary appliances and standard mixer tap
Item number	R8684000
Materials	Lifting unit and baskets: Powder-laquered steel. Worktop: ABS with acrylic. Waste pipe: Polyurethane, PVC and steel. The flexible waste pipe is very resistant to both chemical and physical influences. It is flame retardant and withstands temperatures from -30°C to +110°C.
Ergonomy	The smooth height adjustment ensures that it is always possible to set the table at an ergonomically correct height. The table descends to a very low position, which offers the advantage that toddlers can easily climb up and down themselves. Thereby unnecessary lifting is avoided.
Features	Easy-to-clean surfaces ensure optimum hygiene. Integrated sink and tap. Integrated safety system prevents entrapment.
Mains connection (V)	230
Actuator (motor)	LA31 Deskline (Linak), 2500N, IPX1
Control box	CBD6 (Linak), IP20
Wired remote control	HB30 (Linak), IPX4
Power consumption (maximum load)	Power consumption by maximum load, watt: 96 W Power consumption by standby: 0,1 W
Warranty	Pressalit makes a commitment to remedy material and manufacturing defects for a period of three years from the invoicing date.













PRESSALIT®

Product	Changing table, 800 x 1400 mm, electrically height adjustable, with sanitary appliances and standard mixer tap
Item number	R8684000
Cleaning	<p>Daycare changing tables</p> <p>The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p>DISINFECTANTS:</p> <p>Clinimax Difficil-S Erisan OXY+ Sprit (husholdningssprit) Suma Bac D10 Virkon Rodalon Desinfektionsspray Lysoformin Spezial CaviCide Sufanios Premium Tvättsprit 70%</p> <p>NON-DISINFECTANTS:</p> <p>Suma Star free D1 Taski 100 Taski 200 Milizid Citro</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p>













Product	Changing table, 800 x 1400 mm, electrically height adjustable, with sanitary appliances and standard mixer tap
Item number	R8684000

Installation in different wall types

	<p>Concrete >B25</p> <p>V8608 - Mounting kit, 6 coach screws Ø10 x 70 - plugs SX12. To be ordered separately.</p>	
	<p>Solid Brick >= Mz12</p> <p>V8608 - Mounting kit, 6 coach screws Ø10 x 70 - plugs SX12. To be ordered separately.</p>	
	<p>Solid Sand Lime Brick >= Hlz12</p> <p>V8608 - Mounting kit, 6 coach screws Ø10 x 70 - plugs SX12. To be ordered separately.</p>	
	<p>Aerated Concrete P4</p> <p>V8658 - Mounting kit, 6 coach screws Ø10 x 70 - plugs GB14. To be ordered separately.</p>	
	<p>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</p> <p>V8608 - Mounting kit, 6 coach screws Ø10 x 70 - plugs SX12. NB! Plugs are not needed. To be ordered separately.</p>	



PRESSALIT®

Product Item number	Changing table, 800 x 1400 mm, electrically height adjustable, with sanitary appliances and standard mixer tap R8684000
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood Wall fasteners (6 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.   
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (2 mm) Wall fasteners (6 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.   
	Drywall (2 x 12,5 mm) water-resistant Mounting in this wall type is not recommended - risk of fatal injury to persons and walls. 

pressalit.com