




Product Item number	Flexible feed and waste system 500/700 mm R2061
Product description	<p> VVS:747472510 NRF:6132522 RSK:7972611 EAN:5708590083605 </p>  <p> The flexible feed and waste systems are needed to ensure the flow of water to and from the height adjustable wash basin brackets. </p> <p> Flexible feed/waste system. For export markets. Feed pipes: 500 mm, waste pipe: 700 mm. Feed pipe, metal braid, with 3/8" coupling and 10 mm copper pipe. Flexible waste pipe, dia. 32 mm. </p>
Materials	<p> The feed pipes are made from SPX plastic, braided with stainless steel. The connecting nuts are 3/8" and made from brass with 10 mm copper pipe. The waste pipe is flexible, corrugated white PVC with a diameter of 32 mm. We do not recommend flushing the waste hose with formaldehyde. The elbow with removable connector is made from PP (polypropylene) with a seal of TPE (thermoplastic elastomer). Maximum temperatures of use are 80°C (continuous use) and 90°C (temporary use). PP is very resistant to water, damp and most organic solvents. The seal is made from EPDM – Temperature of use from -50°C - +120°C/150°C EPDM is particularly resistant to ozone and weather. Good resistance to heat and cold and to most chemicals – but poor resistance to petroleum products and solvents. </p>
Ergonomy	<p> To maximize product flexibility, it is important that the plumbing installation are correctly positioned and do not obstruct movement. The waste hose can be shortened on site to fit the installation. </p>
Features	<p> Pressalit supply a kit of flexible feed pipes for hot and cold water along with a flexible waste hose. The kit starts where the feed pipes attach at the isolating valves (not included) and ends where the waste kit meets the existing waste or trap in/at the wall. It assumes a connector that will fit Pressalit's Ø32 mm waste elbow. Adapters for larger connectors, e.g. Ø40 mm, must be ordered separately (not UK). </p>
Warranty	<p> Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date. </p>



PRESSALIT®

Product	Flexible feed and waste system 500/700 mm
Item number	R2061
Cleaning	<p>Flexible feed and waste systems</p> <p>When cleaning the wash basin, it is recommended that one flush the waste hose through with 50-60 degrees hot water in order to prevent build-up of soap residues inside the hose. Ensure that the hose is stretched out during this flushing.</p>

pressalit.com

Pressalit A/S
Pressalitvej 1
DK-8680 Ry
Tel.: +45 8788 8788
Fax: +45 8788 8789
E-mail: pressalit@pressalit.com

PRESSALIT®