




<b>Product</b> <b>Item number</b>	PLUS handrail section 790 mm, incl. wall rosette and strap RT332000
<b>Colour</b>	VVS:777569320 NRF:6311265 EAN:5708590146638 NBS:N13:436  White
<b>Product description</b>	<div>  <div>           RT330 - A = 365            RT331 - A = 662            RT332 - A = 790            RT333 - A = 1090         </div> </div> <p>           PLUS hand rail tube, with wall rosette and strop.            Length 790 mm, diameter 33 mm.            Requires other hand rail elements for installation.  <i>Please enquire for special hand rail solutions.</i>            Excl. mounting kit.            See Technical datasheet (pdf) for information on fixings suitable for various wall types.         </p> <p>           PLUS hand rail tube, with wall rosette and strop.            Length 790 mm, diameter 33 mm.            Requires other hand rail elements for installation.  <i>Please enquire for special hand rail solutions.</i>            Materials: Powder-coated aluminium and plastics.            Excl. mounting kit.         </p>
<b>Product capacity</b>	Maximum load: With a span up to 1000 mm: 210 kg With a span up to 1300 mm: 150 kg.
<b>Materials</b>	Basic material: Aluminium  Surface material: Polyester lacquer  Cover cap: Cyclopy plastic  Strap: Nylon (PA)
<b>Ergonomy</b>	The 33 mm diameter enables the rail to be held comfortably and firmly. The projection of 50 mm from the wall makes it easy to take hold of the rail.
<b>Warranty</b>	Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.



# PRESSALIT<sup>®</sup>











<b>Product</b>	PLUS handrail section 790 mm, incl. wall rosette and strap
<b>Item number</b>	RT332000
<b>Cleaning</b>	The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.










PRESSALIT®

<b>Product</b>	PLUS handrail section 790 mm, incl. wall rosette and strap
<b>Item number</b>	RT332000

## Installation in different wall types

	<p><b>Concrete &gt;B25</b></p> <p>V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p>	
	<p><b>Solid Brick &gt;= Mz12</b></p> <p>V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p>	
	<p><b>Solid Sand Lime Brick &gt;= Hlz12</b></p> <p>V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p>	
	<p><b>Aerated Concrete P4</b></p> <p>V8665 - Mounting kit, 4 bolts M5 x 50 - plugs FTP K 6. To be ordered separately.</p>	
	<p><b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</b></p> <p>V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8. NB! Plugs are not needed. To be ordered separately.</p>	



<b>Product</b> <b>Item number</b>	PLUS handrail section 790 mm, incl. wall rosette and strap RT332000		
	<b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood</b> Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.		
	<b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (2 mm)</b> Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.		
	<b>Drywall (2 x 12,5 mm) water-resistant</b> Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.	