




PRESSALIT®

Product Item number	Dual flush button for PLUS support arm R9342
Product description	VVS:615859300 NRF:6190666 EAN:5708590314686 NBS:N13:436  Flush button can be used with PLUS support arms and SELECT TL2 toilet lifter. Flush button, battery operated (2 x 1½ Volt AAA), for mounting to underside of PLUS support arm. Interconnection with SELECT toilet lifter can be handled by Pressalit. In that case, R9343 (battery) or R9344 (mains) must be added to the order. The flush button also works with selected cisterns from Geberit, please note that further Geberit parts are required.
Materials Features Warranty	PA The flush button for attachment to PLUS support arms comes with 2 buttons: Combination blue/green: Blue button = big flush (lots of water) Green button = small flush (not so much water). Combination blue/black: Blue button = big flush (lots of water) Black button = small flush (not so much water). Combination black/green: Black button = big flush (lots of water) Green button = small flush (not so much water) Combination red/black: Red button = big flush (lots of water) Black button = small flush (not so much water). Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.



PRESSALIT®

Product	Dual flush button for PLUS support arm
Item number	R9342

pressalit.com

Pressalit A/S
Pressalitvej 1
DK-8680 Ry
Tel.: +45 8788 8788
Fax: +45 8788 8789
E-mail: pressalit@pressalit.com

PRESSALIT®