




# PRESSALIT®

|                            |                                                                                                                                                                                                                                                                                              |
|----------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Product</b>             | Mounting kit V8660 (8 pcs), for aerated concrete                                                                                                                                                                                                                                             |
| <b>Item number</b>         | V8660                                                                                                                                                                                                                                                                                        |
| <b>Product description</b> | EAN:5708590351346                                                                                                                                                                                                                                                                            |
|                            |                                                                                                                                                                                                           |
| <b>Product description</b> | Mounting kit, 8 bolts M8 x 35, plugs FTP M 8, for aerated concrete.                                                                                                                                                                                                                          |
|                            | Used for:<br>PLUS wall tracks (vertical): R9873, R9874<br>PLUS support arms: R370370, R370470<br>R370385, R370485<br>PLUS folding seat: R5520<br>PLUS wash basin bracket: R4550<br>PLUS shower seats: R7414, R7415<br><br>Mounting kit, 8 bolts M8 x 35, plugs FTP M 8, for aerated concrete |
| <b>Materials</b>           | Stainless steel                                                                                                                                                                                                                                                                              |

[pressalit.com](http://pressalit.com)

# PRESSALIT®