




Product Item number	Changing table, 800 x 900 mm, electrically height adjustable R8711000
Colour Product description	<p>VVS:777630010 NRF:7501909 RSK:8565142 EAN:5708590286181 HMI: 48861 White</p>  <p>Pressalit offers a wide range of daycare changing tables, both free-standing and wall-hung, in several sizes and models. The wall-hung tables are also available in versions where the worktop folds away, which are suitable for rooms with limited space. Of particular use to daycare facilities and kindergartens are the low start wall-hung changing tables, which can be lowered to a height that allows children to climb onto the worktop themselves.</p> <p>All types of daycare changing tables are available in versions with sanitary appliances and a choice of taps, with or without pull-out shower heads.</p> <p>Wallhung changing table, 800 x 900 mm. With electric motor and transformer, height adjustable from 650 mm - 1000 mm, with wired hand control. Molded worktop, incl. 2 wire baskets. Materials: ABS plastics, synthetic acrylic and powder-lacquered steel. Excl. mounting kit.</p>
Adjustability Adjustment height Product capacity Speed upwards Noise level	Height adjustable 350 mm Max load: 75 kg. Speed up mm: 14 mm/s Speed down mm: 14 mm/s 48 dB
Materials Ergonomy	Lifting unit and baskets: Powder-laquered steel. Worktop: ABS with acrylic. The smooth height adjustment ensures that it is always possible to set the table at an ergonomically correct height.



Product	Changing table, 800 x 900 mm, electrically height adjustable
Item number	R8711000
Features	Easy-to-clean surfaces ensure optimum hygiene.
Mains connection (V)	230
Actuator (motor)	LA31 Deskline (Linak), 1500N, IPX1
Control box	CBD6 (Linak), IP20
Wired remote control	HB30 (Linak), IPX4
Power consumption (maximum load)	Power consumption by maximum load, watt: 96 W Power consumption by standby: 0,1 W
Warranty	Pressalit makes a commitment to remedy material and manufacturing defects for a period of three years from the invoicing date.
Cleaning	<p>The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p>DISINFECTANTS: Clinimax Difficil-S Erisan OXY+ Sprit (husholdningsprit) Suma Bac D10 Virkon Rodalon Desinfektionsspray Lysoformin Spezial CaviCide Sufanios Premium Tvättsprit 70%</p> <p>NON-DISINFECTANTS: Suma Star free D1 Taski 100 Taski 200 Milizid Citro</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p>













PRESSALIT®

Product	Changing table, 800 x 900 mm, electrically height adjustable
Item number	R8711000
WEEE	Please enquire of your local Pressalit subsidiary or distributor (in countries where there is no subsidiary) that will arrange for recycling of electronic waste in accordance with the WEEE directive.








Product	Changing table, 800 x 900 mm, electrically height adjustable
Item number	R8711000

Installation in different wall types

	Concrete >B25 V8608 - Mounting kit, 6 coach screws Ø10 x 70 - plugs SX12. To be ordered separately.	
	Solid Brick >= Mz12 V8608 - Mounting kit, 6 coach screws Ø10 x 70 - plugs SX12. To be ordered separately.	
	Solid Sand Lime Brick >= Hlz12 V8608 - Mounting kit, 6 coach screws Ø10 x 70 - plugs SX12. To be ordered separately.	
	Aerated Concrete P4 V8658 - Mounting kit, 6 coach screws Ø10 x 70 - plugs GB14. To be ordered separately.	
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood V8608 - Mounting kit, 6 coach screws Ø10 x 70 - plugs SX12. NB! Plugs are not needed. To be ordered separately.	



Product Item number	Changing table, 800 x 900 mm, electrically height adjustable R8711000	
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood Wall fasteners (6 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.	
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (2 mm) Wall fasteners (6 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.	
	Drywall (2 x 12,5 mm) water-resistant Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.	