




<b>Product</b> <b>Item number</b>	PLUS handrail section 1090 mm, incl. wall rosette and strap RT333035
<b>Colour</b>  <b>Product description</b>	<p>VVS:777569335          EAN:5708590146799          NBS:N13:436</p> <p>Red (RAL 3003)</p>  <p>RT330 - A = 365          RT331 - A = 662          RT332 - A = 790          RT333 - A = 1090</p> <p>PLUS hand rail tube, with wall rosette and strop.          Length 1090 mm, diameter 33 mm.          Requires other hand rail elements for installation.  <i>Please enquire for special hand rail solutions.</i>          Excl. mounting kit.          See Technical datasheet (pdf) for information on fixings suitable for various wall types.</p> <p>PLUS hand rail tube, with wall rosette and strop.          Length 1090 mm, diameter 33 mm.          Requires other hand rail elements for installation.  <i>Please enquire for special hand rail solutions.</i>          Materials: Powder-coated aluminium and plastics.          Excl. mounting kit.</p>
<b>Product capacity</b>	Maximum load: With a span up to 1000 mm: 210 kg With a span up to 1300 mm: 150 kg.
<b>Materials</b>  <b>Ergonomy</b>	<p>Basic material: Aluminium</p> <p>Surface material: Polyester lacquer</p> <p>Cover cap: Cycoloy plastic</p> <p>Strap: Nylon (PA)</p> <p>The 33 mm diameter enables the rail to be held comfortably and firmly. The projection of 50 mm from the wall makes it easy to take hold of the rail.</p>
<b>Warranty</b>	Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.













# PRESSALIT®

<b>Product</b>	PLUS handrail section 1090 mm, incl. wall rosette and strap
<b>Item number</b>	RT333035
<b>Cleaning</b>	The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.








<b>Product</b>	PLUS handrail section 1090 mm, incl. wall rosette and strap
<b>Item number</b>	RT333035

## Installation in different wall types

	<b>Concrete &gt;B25</b> V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.	
	<b>Solid Brick &gt;= Mz12</b> V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.	
	<b>Solid Sand Lime Brick &gt;= Hlz12</b> V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.	
	<b>Aerated Concrete P4</b> V8665 - Mounting kit, 4 bolts M5 x 50 - plugs FTP K 6. To be ordered separately.	
	<b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</b> V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8. NB! Plugs are not needed. To be ordered separately.	



<b>Product</b> <b>Item number</b>	PLUS handrail section 1090 mm, incl. wall rosette and strap RT333035
	<b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood</b> Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar. 
	<b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (2 mm)</b> Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar. 
	<b>Drywall (2 x 12,5 mm) water-resistant</b> Mounting in this wall type is not recommended - risk of fatal injury to persons and walls. 