



# PRESSALIT®

|                                      |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |
|--------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Product</b><br><b>Item number</b> | PLUS grab bar section 11.8"<br>RT300112                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |
| <b>Color</b>                         | VVS:777569002<br>NRF:6311246<br>EAN:5708590318820<br>NBS:N13:436<br><br>Anthracite gray                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |
| <b>Product description</b>           | <p>PLUS grab bar tube, incl. connecting unit with male and female joints<br/>Length 11.8", diameter 1.3".<br/>Requires other grab bar elements for installation.<br/><i>Please enquire for special grab bar solutions.</i><br/>Please note that RT360 PLUS grab bar wall mounting with strap must always be installed at all joints of tubes or every 47".</p> <p>PLUS grab bar tube, incl. connecting unit with male and female joints<br/>Length 11.8", diameter 1.3".<br/>Requires other grab bar elements for installation.<br/><i>Please enquire for special grab bar solutions.</i><br/>Please note that RT360 PLUS grab bar wall mounting with strap must always be installed at all joints of tubes or every 47".<br/>Materials: Powder-coated aluminium.</p> |
| <b>Product capacity</b>              | Maximum load: With a span up to 39.4" : 460 lbs.<br>With a span up to 51.2" : 330 lbs.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |
| <b>Materials</b>                     | Core material: Aluminium<br>Surface material: Polyester lacquer                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |
| <b>Ergonomy</b>                      | The 1.3" diameter enables the rail to be held comfortably and firmly. The projection of 2" from the wall makes it easy to take hold of the rail.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |
| <b>Warranty</b>                      | Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |
| <b>Cleaning</b>                      | This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |



# PRESSALIT®

|                    |                             |
|--------------------|-----------------------------|
| <b>Product</b>     | PLUS grab bar section 11.8" |
| <b>Item number</b> | RT300112                    |

---

[pressalit.com](http://pressalit.com)

---

Pressalit A/S  
Pressalitvej 1  
DK-8680 Ry  
Tel.: +45 8788 8788  
Fax: +45 8788 8789  
E-mail: [pressalit@pressalit.com](mailto:pressalit@pressalit.com)

## PRESSALIT®