




Product Item number	Pressalit Public Premium Hand dryer with sensor, matte black PX40515
Product description	<p>VVS:776133331 NRF:1438622 RSK:8865105 EAN:5708590395524</p>  <p>Stainless steel warm air hand dryer for wall mounting. Low-noise fan with sensor activated at 172mm (± 20 mm). Drying time approx. 15 sec. Connection for fixed installation or installation via circuit breaker. Permanent installation must be carried out by an authorized electrician</p> <p>Power 840-1000 W. 230 V / 50/60 Hz</p>
Materials	European stainless steel (AISI 304)
Warranty	A 2-year warranty is provided for material and manufacturing defects.
Cleaning	The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.
WEEE	<p>Please enquire of your local Pressalit subsidiary or distributor (in countries where there is no subsidiary) that will arrange for recycling of electronic waste in accordance with the WEEE directive.</p> <p>Subject to changes in the product range, technical changes and printing errors.</p>



PRESSALIT®

Product	Pressalit Public Premium Hand dryer with sensor, matte black
Item number	PX40515

pressalit.com

Pressalit A/S
Pressalitvej 1
DK-8680 Ry
Tel.: +45 8788 8788
Fax: +45 8788 8789
E-mail: pressalit@pressalit.com

PRESSALIT®