




# PRESSALIT®

|                                      |                                                                                                                                                                                                                                                                                                                                                                      |
|--------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Product</b><br><b>Item number</b> | Pressalit Choice Shelf with glassplate 58,8 x 13,5 cm, polished steel<br>Q10400                                                                                                                                                                                                                                                                                      |
| <b>Product description</b>           | <p>VVS:772471540<br/>NRF:6190934<br/>RSK:8892164<br/>EAN:5708590336916</p>  <p>Let the Pressalit Choice bathroom accessory series elevate the décor of your bathroom and create coherence with a timeless look. You get a complete range of accessories to suit any bathroom.</p> |
| <b>Materials</b>                     | Stainless steel AISI 304, glass, mounting knot in brass                                                                                                                                                                                                                                                                                                              |
| <b>Warranty</b><br><b>Cleaning</b>   | <p>A 2-year warranty is provided for material and manufacturing defects.</p> <p>The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.</p> <p>Subject to changes in the product range, technical changes and printing errors.</p>                |

[pressalit.com](http://pressalit.com)