




# PRESSALIT®

<b>Product</b> <b>Item number</b>	Faucet with long rotatable spout and loop-shaped operating lever RT624
<b>Product description</b>	<p>VVS: 701399104  EAN: 5708590382470  HMI: 61272</p>  <p>Faucet with long rotatable spout and loop-shaped operating lever. 6.9" flex hose. Hot and cold symbols. With water-saving Eco-effect. Without drain fitting. We recommend T4679 plumbing kit with 0.4" compatible adaptor.</p> <p>Faucet with long rotatable spout and loop-shaped operating lever. 6.9" flex hose. Hot and cold symbols. With water-saving Eco-effect. Without drain fitting. We recommend T4679 plumbing kit with 0.4" compatible adaptor. Material: Chromium-plated brass</p>
<b>Materials</b>	Chromium-plated brass
<b>Ergonomy</b>	<p>The loop-shaped operating lever is specifically suitable for users who find it difficult to use common levers.</p> <p>The long, rotatable spout makes it easier for a seated user to reach the water, as well as the spout can be swung to one side.</p>
<b>Features</b>	<p>Long rotatable spout.</p> <p>The water-saving Eco-effect gives the choice between a moderate flow and a full flow. The preset moderate flow can be adjusted.</p>
<b>Warranty</b>	Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.
<b>Cleaning</b>	This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.



# PRESSALIT®

<b>Product</b>	Faucet with long rotatable spout and loop-shaped operating lever
<b>Item number</b>	RT624

---

[pressalit.com](http://pressalit.com)

---

Pressalit A/S  
Pressalitvej 1  
DK-8680 Ry  
Tel.: +45 8788 8788  
Fax: +45 8788 8789  
E-mail: [pressalit@pressalit.com](mailto:pressalit@pressalit.com)

# PRESSALIT®