




# PRESSALIT®

|                                      |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
|--------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Product</b><br><b>Item number</b> | Pressalit Style Toilet brush, matt black<br>PR40800                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
| <b>Product description</b>           | <p>           VVS:778496131<br/>           NRF:7001552<br/>           RSK:8714313<br/>           EAN:5708590375373<br/>           DB: 2266869         </p>  <p>           Let elegance and your personal style shine through with Pressalit Style. The long, elegant, graphic shapes will lend an exciting touch to your bathroom. Not only will your bathroom get an aesthetic makeover - it will also reflect the fact that you have made an active decision to welcome extraordinary Danish design into the décor of your home. The products are easy to fit - either with the screws included or with glue, which is purchased separately.         </p> <p>           Give your bathroom an extra boost with this beautifully designed toilet brush. You can stand it on the floor or attach it to the wall. The discreet rubber ring on the bottom ensures greater stability on the floor.         </p> |
| <b>Materials</b>                     | Stainless steel AISI 304, Aluminum alloy, Zinc alloy and PP                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |
| <b>Warranty</b><br><b>Cleaning</b>   | <p>A 2-year warranty is provided for material and manufacturing defects.</p> <p>The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.</p> <p>Subject to changes in the product range, technical changes and printing errors.</p>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |



# PRESSALIT®

|                    |                                          |
|--------------------|------------------------------------------|
| <b>Product</b>     | Pressalit Style Toilet brush, matt black |
| <b>Item number</b> | PR40800                                  |

---

[pressalit.com](http://pressalit.com)

---

Pressalit A/S  
Pressalitvej 1  
DK-8680 Ry  
Tel.: +45 8788 8788  
Fax: +45 8788 8789  
E-mail: [pressalit@pressalit.com](mailto:pressalit@pressalit.com)

# PRESSALIT®

24. september 2026