




PRESSALIT®

Product Item number	Touchless wash basin mixer tap RT631
Product description	VVS: 704388104 NRF: 6132551 EAN: 5708590297354 HMI: 123754 NBS: N13:30,335  Touchless wash basin mixer tap with scalding protection. WRAS-approved.
Features	Temperature adjustment. Battery-operated 6 V. Flow controller (5 l/min.) Infrared sensor technology Protection against scalding
Warranty	Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.
Cleaning	The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.
WEEE	Please enquire of your local Pressalit subsidiary or distributor (in countries where there is no subsidiary) that will arrange for recycling of electronic waste in accordance with the WEEE directive.



PRESSALIT®

Product	Touchless wash basin mixer tap
Item number	RT631

pressalit.com

Pressalit A/S
Pressalitvej 1
DK-8680 Ry
Tel.: +45 8788 8788
Fax: +45 8788 8789
E-mail: pressalit@pressalit.com

PRESSALIT®

24. september 2026