




PRESSALIT®

|                                      |                                                                                                                                                                                                                                                                                                                                                                                                     |
|--------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Product</b><br><b>Item number</b> | Mounting kit V8602 (2 pcs),for brick wall<br>V8602                                                                                                                                                                                                                                                                                                                                                  |
| <b>Product description</b>           | <p>EAN:5708590366012</p>  <p>Mounting kit, 2 coach screws Ø10 x 100 , plugs SX12, for brick wall.</p> <p>Used for:<br/>MATRIX SMALL wash basins: R2020/R2022, R2021/R2023<br/>MATRIX CURVE wash basins: R2050, R2051, R2052, R2053</p> <p>Mounting kit, 2 coach screws Ø10 x 100, plugs SX12, for brick wall</p> |
| <b>Materials</b>                     | Stainless steel and plastic                                                                                                                                                                                                                                                                                                                                                                         |

pressalit.com