




# PRESSALIT®

|                                      |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |
|--------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Product</b><br><b>Item number</b> | Pressalit Public Classic Waste bin 60 l, brushed steel<br>PY30920                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |
| <b>Product description</b>           | <p>VVS:777744615<br/>NRF:1438611<br/>RSK:8920395<br/>EAN:5708590392370</p>  <p>Stainless steel waste bin for floor mounting or concealed wall mounting. Front panel with a stainless steel plate with rounded corners. Equipped with removable, washable polypropylene fabric bag. Capacity approx. 60 liters. Comes with mounting kit.</p> <p>2.5 mm and 4 mm thick grating and mounting holes placed in the second row for concealed wall mounting.</p> |
| <b>Materials</b>                     | European stainless steel (AISI 304)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |
| <b>Warranty</b><br><b>Cleaning</b>   | <p>A 2-year warranty is provided for material and manufacturing defects.</p> <p>The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.</p> <p>Subject to changes in the product range, technical changes and printing errors.</p>                                                                                                                                                                                        |

[pressalit.com](http://pressalit.com)