




# PRESSALIT®

---

## Raised buffer with screw 100 mm

---

<b>Item number</b>	T9804 EAN:5708590183930
<b>Description</b>	Raised buffer with screw 100 mm Raised buffer with screw 100 mm



---

### Product capacity

---

<b>Weight</b>	0,1 kg
<b>Gross weight</b>	0,1 kg
<b>Weight per crate</b>	0 kg
<b>Qty per crate</b>	0
<b>Qty per pallet</b>	0

The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.

---

[pressalit.com](http://pressalit.com)

---