



Product Service

CERTIFICATE

No. Z1 084376 0001 Rev. 00

Model(s): R3070/RF070, R3085/RF085, R3117/RF117, R3127/RF127, R3107/RF107, R3108/RF108, R3165/RF165, R3170/RF170, R3175/RF175, R3185/RF185, R3285, R3565/RF565, R3570/RF570, R3575/RF575, R3585/RF585

Brand Name: Pressalit

Parameters:

Type:	Handle diameter:	Max. length:	Mounting plate:	Max. user weight:	
R3070/RF070	50 mm	700 mm	210 x 100 mm	150 kg	
R3085/RF085		850 mm			
R3117/RF117		730 mm	150 (424) x 128 mm		
R3127/RF127					
R3165/RF165					
R3170/RF170		770 mm			
R3565/RF565					
R3570/RF570		920 mm			
R3575/RF575					
R3585/RF585					
R3107/RF107		880 mm			175 x 104 mm
R3108/RF108					
R3175/RF175					
R3185/RF185					
R3285					
Material:	Aluminum, Stainless steel, SEBS and ABS				

Tested according to: ISO 17966:2016

Production Facility(ies): 084376

ZERTIFIKAT • CERTIFICATE • CERTIFICADO • CERTIFIKAT • 認證書 • CERTIFICATE • CERTIFICATE