



<b>Product</b> <b>Item number</b>	PLUS grab bar, corner 30" x 18.7" RT124108
<b>Color</b>	VVS:777568208 NRF:6317182 EAN:5708590154046 HMI: 25425 NBS:N13:436 Dark blue (RAL 5011)
<b>Product description</b>	<p>PLUS grab bars are high-quality products and they can be combined in countless ways and they provide the final touch to furnishing a functional and flexible bathroom. A reliable solution with many different options, which can easily lay the grounds for increased independence.</p> <p>PLUS grab bar, corner, diameter 1.3", reversible right/left A:30" x B:18.7". Material: Powder-coated aluminium and plastic. Excl. mounting kit.</p>
<b>Product capacity</b>	Maximum load: 440 lbs. When the grab bar is loaded with 440 lbs, each wall fastener is loaded with 123 lbs. <i>Grab bars are tested with a 1.5 safety factor in accordance with the requirements in ISO 17966:2016.</i>
<b>Materials</b>	Core material: Aluminium Surface material: Polyester lacquer Cover cap: Cycloy plastic Strap: Nylon (PA)
<b>Ergonomy</b>	The 1.3" diameter enables the rail to be held comfortably and firmly. The projection of 2" from the wall makes it easy to take hold of the rail.
<b>Warranty</b>	Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.










<b>Product</b>	PLUS grab bar, corner 30" x 18.7"
<b>Item number</b>	RT124108

## Mounting in different wall types

	<p><b>Concrete &gt;B25</b>  V8617 - Mounting kit, 12 bolts Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p>	
	<p><b>Solid Brick &gt;= Mz12</b>  V8617 - Mounting kit, 12 bolts Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p>	
	<p><b>Solid Sand Lime Brick &gt;= Hlz12</b>  V8617 - Mounting kit, 12 bolts Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p>	
	<p><b>Aerated Concrete P4</b>  V8667 - Mounting kit, 12 bolts M5 x 50 - plugs FTP K 6, for aerated concrete. To be ordered separately.</p>	
	<p><b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</b>  V8617 - Mounting kit, 12 bolts Ø5 x 50 - plugs SX8. NB!  Plugs are not needed.  To be ordered separately.</p>	



<b>Product</b> <b>Item number</b>	PLUS grab bar, corner 30" x 18.7" RT124108
	<b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood</b> Wall fasteners (12 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or Wingt anchors or similar. 
	<b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (.08 inch)</b> Wall fasteners (12 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or Wingt anchors or similar. 
	<b>Drywall (2 x 12,5 mm) water-resistant</b> Mounting in this wall type is not recommended - risk of fatal injury to persons and walls. 