




PRESSALIT®

Product Item number	VALUE support arm, fixed height R1100108
Colour	EAN: 5708590235653 HMI: 25411 Dark blue (RAL 5011)
Product description	<p> VALUE support arm, fixed, foldable, projection 850 mm. The ergonomic design gives a secure and comfortable grip as well as a good sense of where the support arm ends. Incl. fixing bolts for brick wall. Plugs depend on wall type and must be ordered separately. </p> <p> VALUE support arm, fixed, foldable, projection 850 mm. The ergonomic design gives a secure and comfortable grip as well as a good sense of where the support arm ends. Materials: Rilsan-coated steel, pressure-cast aluminium, plastic. Incl. fixing bolts for brick wall. Plugs depend on wall type and must be ordered separately. </p>
Adjustability Product capacity	Fixed mounting Maximum load: 120 kg. When the support arm is loaded with 120 kg, each wall fastener is loaded with 242 kg.
Materials Ergonomy Features	<p> The support arm is manufactured from steel with a Rilsan coating, which is comfortable to the touch, easy to clean, and protects the metal against corrosion. The end caps are manufactured from nylon (PA). </p> <p> Provides firm support when you are sitting, standing, or transferring to and from a toilet. </p> <p> Good, broad support surface for the hand and arm. The rounded form gives a firm and comfortable grip. </p> <p> The support arm can fold up when not in use or to make more space. </p>
Warranty	Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.















Product	VALUE support arm, fixed height
Item number	R1100108
Cleaning	<p>VALUE support arms.</p> <p>The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>For surface disinfection, chlorine-based disinfectants may be used according to the product specification and safety precautions for these products.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p>DISINFECTANTS:</p> <p>Clinimax Difficil-S Erisan OXY+ Sprit (husholdningssprit) Suma Bac D10 Virkon Rodalon Desinfektionsspray Lysoformin Spezial CaviCide Sufanios Premium Tvättsprit 70% WipeClean UniversalCleaning Chlorine Disinfection Wipes Klorilli (Kiilto Clean)</p> <p>NON-DISINFECTANTS:</p> <p>Suma Star free D1 Taski 100 Taski 200 Milizid Citro</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p>
Declaration of conformity	CE MDR This product is in compliance with all relevant requirements of: - Regulation (EU) 2017/745 on medical devices.









Product	VALUE support arm, fixed height
Item number	R1100108

Installation in different wall types

	<p>Concrete >B25</p> <p>V8593 - 4 countersunk screws Ø10 x 80, with white screw covers are included. Plugs to be ordered separately.</p>	
	<p>Solid Brick >= Mz12</p> <p>V8593 - 4 countersunk screws Ø10 x 80, with white screw covers are included. Plugs to be ordered separately.</p>	
	<p>Solid Sand Lime Brick >= Hlz12</p> <p>V8593 - 4 countersunk screws Ø10 x 80, with white screw covers are included. Plugs to be ordered separately.</p>	
	<p>Aerated Concrete P4</p> <p>V8593 - 4 countersunk screws Ø10 x 80, with white screw covers are included. Plugs to be ordered separately.</p>	
	<p>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</p> <p>V8593 - 4 countersunk screws Ø10 x 80, with white screw covers are included. Plugs to be ordered separately.</p>	



Product Item number	VALUE support arm, fixed height R1100108
	<p>Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood</p> <p>Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.</p> 
	<p>Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (2 mm)</p> <p>Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.</p> 
	<p>Drywall (2 x 12,5 mm) water-resistant</p> <p>Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.</p> 

Bolts for wall fixing are included. It is the responsibility of the installer to ensure that suitable plugs are used. Please see mounting instruction.