




PRESSALIT®

Product Item number	VALUE tube 234 mm R1314000
Colour	<p>VVS:777546200 NRF:6311123 EAN:5708590168968 NBS:N13:436</p> <p>White</p> 
Product description	<p>Tube ABS, 234 mm, diameter 32 mm Note: An ABS solvent weld must be used. Pressalit Care recommends Cyanolit (Pressalit Care no T4654).</p> <p>VALUE tube 234 mm, diameter 32 mm. Material: Solid colour ABS plastic. Note: An ABS solvent weld must be used. Pressalit recommends Cyanolit (Pressalit no T4654).</p>
Adjustability	Fixed mounting
Product capacity	Maximum load: For a span up to 600 mm: 100 kg.
Materials Ergonomy	<p>The handrail is made from solid colour ABS plastic tubing so scratches and ordinary wear cannot be seen.</p> <p>The 32 mm diameter enables the rail to be held comfortably and firmly. The projection of 50 mm from the wall makes it easy to take hold of the rail. The grooved surface gives an extra grip.</p>
Warranty	Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.



PRESSALIT®

Product	VALUE tube 234 mm
Item number	R1314000
Cleaning	<p>UDGÅET Handrails ABS.</p> <p>The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>For surface disinfection, chlorine-based disinfectants may be used according to the product specification and safety precautions for these products.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p>DISINFECTANTS: Clinimax Difficil-S Erisan OXY+</p> <p>NON-DISINFECTANTS: Suma Star free D1 Taski 100 Taski 200</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p>

pressalit.com

PRESSALIT®