




PRESSALIT®

Product Item number	VALUE 90° angle uden tap R1345000
Colour	VVS:777547600 NRF:6311131 EAN:5708590169378 NBS:N13:436 White
Product description	 Angle 90° without plug ABS, diameter 32 mm Note: An ABS solvent weld must be used. Pressalit Care recommends Cyanolit (Pressalit Care no T4654). VALUE angle 90° without plug diameter 32 mm. Material: Solid colour ABS plastic. Note: An ABS solvent weld must be used. Pressalit recommends Cyanolit (Pressalit no T4654).
Adjustability	Fixed mounting
Materials	The handrail is made from solid colour ABS plastic tubing so scratches and ordinary wear cannot be seen.
Warranty	Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.



PRESSALIT®

Product	VALUE 90° angle uden tap
Item number	R1345000
Cleaning	<p>UDGÅET Handrails ABS. The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use corrosive or abrasive cleaners as it may result in the surface being damaged. For surface disinfection, chlorine-based disinfectants may be used according to the product specification and safety precautions for these products.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p>DISINFECTANTS: Clinimax Difficil-S Erisan OXY+</p> <p>NON-DISINFECTANTS: Suma Star free D1 Taski 100 Taski 200</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p>

pressalit.com

PRESSALIT®