



# PRESSALIT®











<b>Product</b> <b>Item number</b>	MATRIX CURVE ergonomic sink with overflow R2050000
<b>Color</b>	VVS:636859100 NRF:6191675 EAN:5708590207957 HMI: 42540 NBS:N13:30,335 White
<b>Product description</b>	<p>MATRIX is a series of sinks, most of them are designed by Pressalit. MATRIX SMALL and CURVE sinks fit onto PLUS, SELECT and VALUE sink brackets, whereas MATRIX MEDIUM and ANGLE are tailor made to fit specific brackets.</p> <p>MATRIX CURVE ergonomic sink, 23.6" x 19.3" x 7.5", with tap hole diameter 1.4", with overflow. Supplied with drain fitting. The concave front edge stabilises standing as well as seated users. The rounded edges are also comfortable to hold and rest against. The flat bottom leaves room for the legs underneath. Material: Ceramic. Suitable for sink brackets from the Pressalit PLUS, SELECT and VALUE ranges.</p>
<b>Product capacity</b>	440 lbs.
<b>Materials</b>	Ceramic
<b>Ergonomy</b>	The concaved front edge stabilizes a standing as well as a seated user. The rounded shapes are nice to grip and lean against. The design of the corners leaves space and supports the elbows in the sink and the flat bottom leaves space for the legs of a seated user.
<b>Warranty</b>	Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.
<b>Declaration of conformity</b>	<b>Declaration of Performance</b> Compliance criteria according to EN 14688:2015. 4.1 Load resistance: Passed. 4.6 Cleanability: Passed. 4.7 Protection against overflowing: CL 25. Durability: Passed









PRESSALIT®

<b>Product</b>	MATRIX CURVE ergonomic sink with overflow
<b>Item number</b>	R2050000

## Mounting in different wall types

	<b>Concrete &gt;B25</b> V8602 - Mounting kit, 2 lag bolts Ø10 x 100 - plugs SX12. To be ordered separately	
	<b>Solid Brick &gt;= Mz12</b> V8602 - Mounting kit, 2 lag bolts Ø10 x 100 - plugs SX12. To be ordered separately	
	<b>Solid Sand Lime Brick &gt;= Hlz12</b> V8602 - Mounting kit, 2 lag bolts Ø10 x 100 - plugs SX12. To be ordered separately	
	<b>Aerated Concrete P4</b> V8652 - Mounting kit, 2 lag bolts Ø10 x 100 - plugs GB14. To be ordered separately.	
	<b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</b> V8602 - Mounting kit, 2 countersunk bolts Ø10 x 80, plugs SX12. NB! Plugs are not needed. To be ordered separately.	



<b>Product</b> <b>Item number</b>	MATRIX CURVE ergonomic sink with overflow R2050000
	<b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood</b> Mounting in this wall type is not recommended - risk of fatal injury to persons and walls. 
	<b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (.08 inch)</b> Mounting in this wall type is not recommended - risk of fatal injury to persons and walls. 
	<b>Drywall (2 x 12,5 mm) water-resistant</b> Mounting in this wall type is not recommended - risk of fatal injury to persons and walls. 

It is the responsibility of the installer to ensure that suitable wall fasteners are used.