



PRESSALIT®

| | |
|----------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Product Item number | Changing table, 31.5" x 35.4", electrically height adjustable R8711000 |
| Color | VVS:777630010 NRF:7501909 EAN:5708590286181 HMI: 48861 White |
| Product description | <p>Pressalit offers a wide variety of changing tables designed for use in daycare facilities. The tables are available in several sizes and models, either free standing or wall-hung. The fold away feature in wall-hung tables is useful where space is limited. The wall-hang tables with low start are essential for daycare or preschool facilities. Even toddlers can climb onto the table themselves, without the staff lifting them.</p> <p>Changing table, wall-mounted, 31.5" x 35.4". With motor and transformer, height adjustable from 25.6" - 39.4", with hand control. Molded worktop, incl. 2 wire baskets. Materials: ABS plastics, synthetic acrylic and powder-lacquered steel. Excl. fixing kit.</p> |
| Adjustability Adjustment height Product capacity Speed up Noise level | Height adjustable 13,79 inch Max load: 165 lbs. Speed up: 0,55 inch/s Speed down: 0,55 inch/s 48 dB |
| Materials Ergonomy Features Mains connection (V) | Lifting unit and baskets: Powder-coated steel. Countertop: ABS with acrylic. The smooth height adjustment ensures that it is always possible to set the table at an ergonomically correct height. Easy-to-clean surfaces ensure optimum hygiene. 230 |













PRESSALIT®

| | |
|-------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Product Item number | Changing table, 31.5" x 35.4", electrically height adjustable R8711000 |
| Actuator (motor) Control box Wired remote control Power consumption (maximum load) | LA31 Deskline (Linak), 1500N, IPX1 CBD6 (Linak), IP20 HB30 (Linak), IPX4 Power consumption by maximum load: 96 W Power consumption by standby: 0,1 W |
| Warranty Cleaning | <p>Pressalit makes a commitment to remedy material and manufacturing defects for a period of three years from the invoicing date.</p> <p>This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p>DISINFECTANTS: CaviCide</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p> |



| | |
|--------------------|---------------------------------------------------------------|
| Product | Changing table, 31.5" x 35.4", electrically height adjustable |
| Item number | R8711000 |

Mounting in different wall types

| | | |
|-------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
|  | <p>Concrete >B25</p> <p>V8608 - Mounting kit, 6 lag bolts Ø10 x 70 - plugs SX12. To be ordered separately.</p> |  |
|  | <p>Solid Brick >= Mz12</p> <p>V8608 - Mounting kit, 6 lag bolts Ø10 x 70 - plugs SX12. To be ordered separately.</p> |  |
|  | <p>Solid Sand Lime Brick >= Hlz12</p> <p>V8608 - Mounting kit, 6 lag bolts Ø10 x 70 - plugs SX12. To be ordered separately.</p> |  |
|  | <p>Aerated Concrete P4</p> <p>V8658 - Mounting kit, 6 lag bolts Ø10 x 70 - plugs GB14. To be ordered separately.</p> |  |
|  | <p>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</p> <p>V8608 - Mounting kit, 6 lag bolts Ø10 x 70 - plugs SX12. NB! Plugs are not needed. To be ordered separately.</p> |  |



PRESSALIT®

| | |
|--------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Product Item number | Changing table, 31.5" x 35.4", electrically height adjustable R8711000 |
| | <p>Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood</p> <p>Wall fasteners (6 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or WingIt anchors or similar.</p> |
| | <p>Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (.08 inch)</p> <p>Wall fasteners (6 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or WingIt anchors or similar.</p> |
| | <p>Drywall (2 x 12,5 mm) water-resistant</p> <p>Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.</p> |

pressalit.com

Pressalit A/S
 Pressalitvej 1
 DK-8680 Ry
 Tel.: +45 8788 8788
 Fax: +45 8788 8789
 E-mail: pressalit@pressalit.com

PRESSALIT®