



Product	Changing table, 800 x 1800 mm, electrically height adjustable, with sanitary appliances and mixer tap with pull-out spout
Item number	R8733000 VVS:777630230 NRF:7501917 EAN:5708590286259 HMI: 48876
Colour	White
Product description	Wallhung changing table, with sanitary appliances, 800 x 1800 mm. With electric motor and transformer, height adjustable from 300 mm - 1000 mm, with wired hand control. Laminate worktop with inset stainless steel sink, incl. lever operated mixer tap, pull-out shower head, feed/waste system and 2 wire baskets. Excl. fixing kit. See Technical datasheet (pdf) for information on fixings suitable for various wall types.
Adjustability	Height adjustable
Adjustment height	350 mm
Product capacity	Max load: 150 kg.
Speed, upwards	Speed up mm: 14 mm/s Speed down mm: 14 mm/s
Noise level	48 dB
Materials	Lifting unit and baskets: Powder-laquered steel. Worktop: Melamine. Waste pipe: Polyurethane, PVC and steel. The flexible waste pipe is very resistant to both chemical and physical influences. It is flame retardant and withstands temperatures from -30°C to +110°C.
Ergonomy	The smooth height adjustment ensures that it is always possible to set the table at an ergonomically correct height.
Features	Easy-to-clean surfaces ensure optimum hygiene. Underglued sink and tap with pull-out spout.
Mains connection (V)	230
Actuator (motor)	2 x LA31 Deskline (Linak), 1500N, IPX1








Product	Changing table, 800 x 1800 mm, electrically height adjustable, with sanitary appliances and mixer tap with pull-out spout
Control box	CBD6 (Linak), IP22
Wired remote control	HB3 (Linak), IP66
Power consumption (maximum load)	Power consumption by maximum load: 96 W Power consumption by standby: 0,1 W
Warranty	Pressalit makes a commitment to remedy material and manufacturing defects for a period of three years from the invoicing date.
Cleaning	<p>Changing table. The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p>DISINFECTANTS: Clinimax Difficil-S Erisan OXY+</p> <p>NON-DISINFECTANTS: Suma Star free D1 Taski 100 Taski 200</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p>
Declaration of conformity	This product complies with the requirements of Council Directive 2006/42/EC (of 17 May 2006) on machinery and the Council Directive 2011/65/EC on RoHS.











Product	Changing table, 800 x 1800 mm, electrically height adjustable, with sanitary appliances and mixer tap with pull-out spout
----------------	---

Installation in different wall types

	Concrete >B25 V8608 - Fixing kit, 6 coach screws Ø10 x 70 - plugs SX12. To be ordered separately.
	Solid Brick >= Mz12 V8608 - Fixing kit, 6 coach screws Ø10 x 70 - plugs SX12. To be ordered separately.
	Solid Sand Lime Brick >= Hlz12 V8608 - Fixing kit, 6 coach screws Ø10 x 70 - plugs SX12. To be ordered separately.
	Aerated Concrete P4 V8658 - Fixing kit, 6 coach screws Ø10 x 70 - plugs GB14. To be ordered separately.
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood V8608 - Fixing kit, 6 coach screws Ø10 x 70 - plugs SX12. NB! Plugs are not needed. To be ordered separately.





<p>Product</p>	<p>Changing table, 800 x 1800 mm, electrically height adjustable, with sanitary appliances and mixer tap with pull-out spout</p>	
	<p>Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood</p> <p>Wall fasteners (6 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.</p>	<p>fischer KD 8 snaptight wingit</p> 
	<p>Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (2 mm)</p> <p>Wall fasteners (6 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.</p>	<p>fischer KD 8 snaptight wingit</p> 
	<p>Drywall (2 x 12,5 mm) water-resistant</p> <p>Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.</p>	



www.pressalit.com