




# PRESSALIT®

<b>Product</b> <b>Item number</b>	Lift for worktop, electrically height adjustable RK1011
<b>Product description</b>	<p> EAN: 5708590265728  HMI: 42885 </p>  <p> The name INDIVO relates to the individual configuration of the products.   Lift for worktop, with 2 motors and switches.  Including 2 brackets and transformer.  Lengths from 1001 mm - 1400 mm.  Height adjustable up to 300 mm.  Incl. mounting kit for brick wall  Please state desired length when ordering </p>
<b>Adjustability</b> <b>Adjustment height</b> <b>Product capacity</b> <b>Speed upwards</b> <b>Noise level</b>	<p> Height adjustable  300 mm   Maximum load (evenly distributed):  100 kg including worktop.  Speed up mm: 20 mm/s  Speed down mm: 20 mm/s  45 dB </p>
<b>Materials</b>  <b>Ergonomy</b>	<p> Material:  Telescopic leg: Aluminium, ABS plastic  Cross braces: Aluminium  Brackets: Steel  Switches: ABS plastic  Surface treatment:  Brackets: Powder lacquered (grey RAL 9006) </p> <p> An electric height-adjustable kitchen worktop is ideal in all situations where various users - both seated and standing - use the same kitchen.  This is equally true in private homes as well as larger centres with common kitchen facilities such as group homes and care centres. </p>



<b>Product</b>	Lift for worktop, electrically height adjustable
<b>Item number</b>	RK1011
<b>Features</b>	<p>Lift heights are adjusted via switches in the front edge.</p> <p>Operating switches can be placed wherever you want in the front edge.</p> <p>The switches are colour-coded - aluminium to operate worktops and red to operate wall cupboards.</p> <p>Lifts can be adapted to most standard kitchen components.</p> <p>Lifts are available for worktops of any length between 600 mm and 3000 mm.</p>
<b>Actuator (motor)</b>	DB4 Deskline (Linak) 1000 N, IP22
<b>Control box</b>	CBD6 (Linak)
<b>Wired remote control</b>	HB53 (Linak), IPX1
<b>Power consumption (maximum load)</b>	<p>Power consumption by maximum load, watt: 300 W</p> <p>Power consumption by standby: 2 W</p>
<b>Warranty</b>	Pressalit makes a commitment to remedy material and manufacturing defects for a period of three years from the invoicing date.



<b>Product</b>	Lift for worktop, electrically height adjustable
<b>Item number</b>	RK1011
<b>Cleaning</b>	<p>INDIVO lift for kitchen worktop. The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p><b>DISINFECTANTS:</b> Clinimax Difficil-S Erisan OXY+ Sprit (husholdningssprit) Suma Bac D10 Virkon Rodalon Desinfektionsspray Lysoformin Spezial CaviCide Sufanios Premium Tvättsprit 70%</p> <p><b>NON-DISINFECTANTS:</b> Suma Star free D1 Taski 100 Taski 200 Milizid Citro</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p> <p><b>DECALCIFICATION OF ALUMINUM PARTS:</b> Pressalit recommends that chalky deposits be removed from wall tracks and other aluminum parts using a solution of three parts 30% acetic acid to seven parts tap water. When the aluminum parts have been washed down with this solution, the parts must be wiped over with a damp cloth wrung out in clear water.</p>



# PRESSALIT®

<b>Product</b>	Lift for worktop, electrically height adjustable
<b>Item number</b>	RK1011

---

[pressalit.com](http://pressalit.com)

---

Pressalit A/S  
Pressalitvej 1  
DK-8680 Ry  
Tel.: +45 8788 8788  
Fax: +45 8788 8789  
E-mail: [pressalit@pressalit.com](mailto:pressalit@pressalit.com)

# PRESSALIT®