




PRESSALIT®

Product Item number	Lift for worktop, electrically height adjustable RK1012
Product description	<p> EAN: 5708590265735 HMI: 42886 </p>  <p> The name INDIVO relates to the individual configuration of the products. Lift for worktop, with 2 motors and switches. Including 3 brackets and transformer. Lengths from 1401 mm - 2000 mm. Height adjustable up to 300 mm. Incl. mounting kit for brick wall Please state desired length when ordering </p>
Adjustability Adjustment height Product capacity Speed upwards Noise level	<p> Height adjustable 300 mm Maximum load (evenly distributed): 100 kg including worktop. Speed up mm: 20 mm/s Speed down mm: 20 mm/s 45 dB </p>
Materials Ergonomy	<p> Material: Telescopic leg: Aluminium, ABS plastic Cross braces: Aluminium Brackets: Steel Switches: ABS plastic Surface treatment: Brackets: Powder lacquered (grey RAL 9006) </p> <p> An electric height-adjustable kitchen worktop is ideal in all situations where various users - both seated and standing - use the same kitchen. This is equally true in private homes as well as larger centres with common kitchen facilities such as group homes and care centres. </p>



Product	Lift for worktop, electrically height adjustable
Item number	RK1012
Features	<p>Lift heights are adjusted via switches in the front edge.</p> <p>Operating switches can be placed wherever you want in the front edge.</p> <p>The switches are colour-coded - aluminium to operate worktops and red to operate wall cupboards.</p> <p>Lifts can be adapted to most standard kitchen components.</p> <p>Lifts are available for worktops of any length between 600 mm and 3000 mm.</p>
Actuator (motor)	DB4 Deskline (Linak) 1000 N, IP22
Control box	CBD6 (Linak)
Wired remote control	HB53 (Linak), IPX1
Power consumption (maximum load)	<p>Power consumption by maximum load, watt: 300 W</p> <p>Power consumption by standby: 2 W</p>
Warranty	Pressalit makes a commitment to remedy material and manufacturing defects for a period of three years from the invoicing date.



Product	Lift for worktop, electrically height adjustable
Item number	RK1012
Cleaning	<p>INDIVO lift for kitchen worktop. The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p>DISINFECTANTS: Clinimax Difficil-S Erisan OXY+ Sprit (husholdningssprit) Suma Bac D10 Virkon Rodalon Desinfektionsspray Lysoformin Spezial CaviCide Sufanios Premium Tvättsprit 70%</p> <p>NON-DISINFECTANTS: Suma Star free D1 Taski 100 Taski 200 Milizid Citro</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p> <p>DECALCIFICATION OF ALUMINUM PARTS: Pressalit recommends that chalky deposits be removed from wall tracks and other aluminum parts using a solution of three parts 30% acetic acid to seven parts tap water. When the aluminum parts have been washed down with this solution, the parts must be wiped over with a damp cloth wrung out in clear water.</p>



PRESSALIT®

Product	Lift for worktop, electrically height adjustable
Item number	RK1012

pressalit.com

Pressalit A/S
Pressalitvej 1
DK-8680 Ry
Tel.: +45 8788 8788
Fax: +45 8788 8789
E-mail: pressalit@pressalit.com

PRESSALIT®