




<p>Product Item number</p>	<p>Lift for worktop, electrically height adjustable RK1012</p>
<p>Product description</p>	<p>EAN:5708590265735 HMI: 42886</p>  <p>The name INDIVO relates to the individual configuration of the products.</p> <p>Lift for worktop, with 2 motors and switches. Including 3 brackets and transformer. Lengths from 1401 mm - 2000 mm. Height adjustable up to 300 mm. Incl. mounting kit for brick wall Please state desired length when ordering</p>
<p>Adjustability Adjustment height Product capacity Speed upwards Noise level</p>	<p>Height adjustable 300 mm Maximum load (evenly distributed): 100 kg including worktop. Speed up mm: 20 mm/s Speed down mm: 20 mm/s 45 dB</p>
<p>Materials Ergonomy</p>	<p>Material: Telescopic leg: Aluminium, ABS plastic Cross braces: Aluminium Brackets: Steel Switches: ABS plastic Surface treatment: Brackets: Powder lacquered (grey RAL 9006)</p> <p>An electric height-adjustable kitchen worktop is ideal in all situations where various users - both seated and standing - use the same kitchen. This is equally true in private homes as well as larger centres with common kitchen facilities such as group homes and care centres.</p>



Product	Lift for worktop, electrically height adjustable
Item number	RK1012
Features	<p>Lift heights are adjusted via switches in the front edge. Operating switches can be placed wherever you want in the front edge. The switches are colour-coded - aluminium to operate worktops and red to operate wall cupboards. Lifts can be adapted to most standard kitchen components. Lifts are available for worktops of any length between 600 mm and 3000 mm.</p>
Actuator (motor)	DB4 Deskline (Linak) 1000 N, IP22
Control box	CBD6 (Linak)
Wired remote control	HB53 (Linak), IPX1
Power consumption (maximum load)	<p>Power consumption by maximum load, watt: 300 W Power consumption by standby: 2 W</p>
Warranty	Pressalit makes a commitment to remedy material and manufacturing defects for a period of three years from the invoicing date.



Product	Lift for worktop, electrically height adjustable
Item number	RK1012
Cleaning	<p>INDIVO lift for kitchen worktop. The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p>DISINFECTANTS: Clinimax Difficil-S Erisan OXY+</p> <p>NON-DISINFECTANTS: Suma Star free D1 Taski 100 Taski 200</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p> <p>DECALCIFICATION OF ALUMINUM PARTS: Pressalit recommends that chalky deposits be removed from wall tracks and other aluminum parts using a solution of three parts 30% acetic acid to seven parts tap water. When the aluminum parts have been washed down with this solution, the parts must be wiped over with a damp cloth wrung out in clear water.</p>