



<p>Product</p> <p>Item number</p>	<p>Lift for wall cupboard, electrically height adjustable</p> <p>RK1020</p>
<p>Product description</p>	<p>EAN:5708590265742</p> <p>HMI: 42887</p> <div data-bbox="1018 481 1348 846" data-label="Image"> </div> <p>The name INDIVO relates to the individual configuration of the products.</p> <p>Lift for wall cupboards, with 1 motor, height adjustable down/out, with switches. Lengths up to 1200 mm. Height adjustable 430 mm. Incl. mounting kit for brick wall Please state desired length when ordering</p>
<p>Adjustability</p> <p>Adjustment height</p> <p>Product capacity</p> <p>Speed upwards</p> <p>Noise level</p>	<p>Height adjustable</p> <p>430 mm</p> <p>Max. load (including cupboards): 1 lift: 110 kg</p> <p>Speed up mm: 18 mm/s Speed down mm: 18 mm/s</p> <p>48 dB</p>
<p>Materials</p> <p>Ergonomy</p>	<p>Material: Lift motor: Steel Cross braces: Aluminium Switches: ABS plastic</p> <p>Wall cupboards are moved diagonally, that is both vertically and towards the user. This makes it easy for seated users and children to see and access covered contents. Height-adjustable wall cupboards provide extra storage options in kitchens where cupboards cannot be installed under worktops out of consideration for seated users.</p>



Product	Lift for wall cupboard, electrically height adjustable
Item number	RK1020
Features	<p>Lift heights for wall cupboards are adjusted via switches in the front worktop edge. Operating switches can be placed wherever you want along the front edge. The switches are colour-coded - aluminium to operate worktops, and red to operate wall cupboards.</p> <p>The design of the lifts ensures that the lift motors are as discreet as possible, regardless of the cupboard position.</p> <p>When the wall cupboards are lowered 430 mm to their lowest position, they are also extended 180 mm towards the user.</p>
Actuator (motor)	LA31 Deskline (Linak), 1500N, IPX1
Control box	CBD6 (Linak)
Wired remote control	HB53 (Linak), IPX1
Power consumption (maximum load)	Power consumption by maximum load, watt: 187 W Power consumption by standby: 1,5 W
Warranty	Pressalit makes a commitment to remedy material and manufacturing defects for a period of three years from the invoicing date.



Product	Lift for wall cupboard, electrically height adjustable
Item number	RK1020
Cleaning	<p>INDIVO lift for kitchenwall cupboard. The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p>DISINFECTANTS: Clinimax Difficil-S Erisan OXY+</p> <p>NON-DISINFECTANTS: Suma Star free D1 Taski 100 Taski 200</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p> <p>DECALCIFICATION OF ALUMINUM PARTS: Pressalit recommends that chalky deposits be removed from wall tracks and other aluminum parts using a solution of three parts 30% acetic acid to seven parts tap water. When the aluminum parts have been washed down with this solution, the parts must be wiped over with a damp cloth wrung out in clear water.</p>