




Product	Lift for worktop, electrically height adjustable
Item number	RK1082 EAN:5708590293783 HMI: 61267
Product description	<p>Electric lift for freestanding worktop. For worktops from 2001 - 2400 mm. Height adjustable 300 mm. Including 2 telescopic legs, brackets, longitudinal and cross braces and switch.</p> <p>Pressalit Care recommends overhang of 400 mm at either end of worktop to allow for ease of approach in wheel-chair.</p> <p>Please state desired length when ordering.</p>
Adjustability	Height adjustable
Adjustment height	300 mm
Product capacity	Maximum load (evenly distributed): 100 kg including worktop.
Speed, upwards	Speed up mm: 20 mm/s Speed down mm: 20 mm/s
Noise level	45 dB
Materials	<p>Material: Telescopic leg: Aluminium, ABS plastic Cross braces: Aluminium Brackets: Steel Cable tray: ABS plastic Switches: ABS plastic Surface treatment: Brackets: Powder lacquered (grey RAL 9006)</p>
Ergonomy	<p>A freestanding electric Indivo solution is a flexible work or dining table, primarily intended for use in the kitchen. The height of the worktop can be quickly and easily adjusted to the given user or situation. A freestanding worktop can also be used in rooms in which the walls are not strong enough to support the wall-mounted models.</p>





Product	Lift for worktop, electrically height adjustable
Features	<p>Lift heights are adjusted via switches set in the edge or directly under the worktop. Operating switches can be placed anywhere.</p> <p>The design of the legs and feet make the table stable and secure, and ensure the lift causes minimal inconvenience to wheelchair users.</p> <p>The design of the lift makes it possible to use the worktop from all sides.</p> <p>Height adjustable over a range of 300 mm.</p> <p>Available for worktops of any length between 1400 mm and 3000 mm.</p>
Actuator (motor)	DB4 Deskline (Linak) 1000 N, IP22
Control box	CBD6 (Linak)
Power consumption (maximum load)	Power consumption by maximum load: 300 W Power consumption by standby: 2 W
Warranty	Pressalit makes a commitment to remedy material and manufacturing defects for a period of three years from the invoicing date.
Cleaning	<p>INDIVO lift for kitchen worktop.</p> <p>The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p>DISINFECTANTS: Clinimax Difficil-S Erisan OXY+</p> <p>NON-DISINFECTANTS: Suma Star free D1 Taski 100 Taski 200</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p> <p>DECALCIFICATION OF ALUMINUM PARTS: Pressalit recommends that chalky deposits be removed from wall tracks and other aluminum parts using a solution of three parts 30% acetic acid to seven parts tap water. When the aluminum parts have been washed down with this solution, the parts must be wiped over with a damp cloth wrung out in clear water.</p>





PRESSALIT®

Product	Lift for worktop, electrically height adjustable
----------------	--



www.pressalit.com

Pressalit A/S
Pressalitvej 1
DK-8680 Ry
Tel.: +45 8788 8788
Fax: +45 8788 8789
E-mail: pressalit@pressalit.com

PRESSALIT®