



Product Item number	Lift for countertop, manually height adjustable RK1110
Product description	<p>EAN:5708590292755 HMI: 54799</p> <p>The name INDIVO relates to the individual configuration of the products.</p> <p>Manual lift for countertop Lift for countertop, with a crank handle Including 2 brackets Lengths from 23.6"-39.4". Height adjustable 11.8". Incl. mounting kit for brick wall Please state desired length when ordering</p>
Adjustability Product capacity	<p>Height adjustable</p> <p>Maximum load (evenly distributed): 220 lbs including countertop.</p>
Materials Ergonomy Features	<p>Material: Telescopic leg: Aluminium, ABS plastic Cross braces: Aluminium Brackets: Steel Crank handle: Steel Surface treatment: Brackets: Powder lacquered (grey RAL 9006)</p> <p>Kitchen countertops which can be adjusted in height using a crank handle are the budget solution for kitchens catering to both seated and standing users. These are most commonly used in kitchens which do not require frequent, daily adjustment.</p> <p>Manual lifts are adjusted in height using a crank handle. They can be used with countertops, with or without an edge. The crank handle socket can be positioned anywhere along the front edge, except under a sink or hob. Lifts can be adapted to most standard kitchen components. Lifts are available for countertops of any length between 23.6" and 118.1". Height adjustable 11.8".</p>



PRESSALIT®

Product	Lift for countertop, manually height adjustable
Item number	RK1110
Warranty	Pressalit makes a commitment to remedy material and manufacturing defects for a period of three years from the invoicing date.
Cleaning	<p>This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p>DISINFECTANTS: CaviCide</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p> <p>DECALCIFICATION OF ALUMINUM PARTS: Pressalit recommends that water deposits (Calcium, lime etc.) be removed from wall tracks and other aluminum parts using a solution of three parts of 30% acetic acid to seven parts tap water. When the aluminum parts have been washed down with this solution, the parts should be wiped over with a damp cloth wrung out in plain water.</p>

pressalit.com

PRESSALIT®