




Product	PLUS handrail 600 mm
Item number	RT102000 VVS:777565300 NRF:6191671 RSK:8980544 EAN:5708590145907 HMI: 19083 NBS:N13:436
Colour	White
Product description	PLUS handrail, diameter 33 mm, length 600 mm, for fixed mounting. The projection of 50 mm from the wall makes it easy to take hold of the rail. Inkl. wall rosette, which covers the fixings. Material: Powder-coated aluminium and plastic Excl. fixing kit. See Technical datasheet (pdf) for information on fixings suitable for various wall types.
Adjustment height Product capacity	Maximum load: 235 kg. When the handrail is loaded with 235 kg, each wall fastener is loaded with 56 kg. <i>Handrails are tested with a 1.5 safety factor in accordance with the requirements in ISO 17966:2016.</i>
Materials	Basic material: Aluminium Surface material: Polyester lacquer Cover cap: Cycoloy plastic
Ergonomy	The 33 mm diameter enables the rail to be held comfortably and firmly. The projection of 50 mm from the wall makes it easy to take hold of the rail.
Warranty	Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.










Product	PLUS handrail 600 mm
Cleaning	<p>Handrails ALU. The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p>DISINFECTANTS: Clinimax Difficil-S Erisan OXY+</p> <p>NON-DISINFECTANTS: Suma Star free D1 Taski 100 Taski 200</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p> <p>DECALCIFICATION OF ALUMINUM PARTS: Pressalit recommends that chalky deposits be removed from wall tracks and other aluminum parts using a solution of three parts 30% acetic acid to seven parts tap water. When the aluminum parts have been washed down with this solution, the parts must be wiped over with a damp cloth wrung out in clear water.</p>










Product	PLUS handrail 600 mm
----------------	----------------------

Installation in different wall types

	<p>Concrete >B25</p> <p>V8616 - Fixing kit, 8 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p>
	<p>Solid Brick >= Mz12</p> <p>V8616 - Fixing kit, 8 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p>
	<p>Solid Sand Lime Brick >= Hlz12</p> <p>V8616 - Fixing kit, 8 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p>
	<p>Aerated Concrete P4</p> <p>V8666 - Fixing kit, 8 bolts M5 x 50 - plugs FTP K 6. To be ordered separately.</p>
	<p>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</p> <p>V8616 - Fixing kit, 8 screws Ø5 x 50 - plugs SX8. NB! Plugs are not needed. To be ordered separately.</p>





Product	PLUS handrail 600 mm	
	<p>Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood</p> <p>Wall fasteners (8 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.</p>	<p>fischer KD 8 snaptight wingit</p> 
	<p>Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (2 mm)</p> <p>Wall fasteners (8 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.</p>	<p>fischer KD 8 snaptight wingit</p> 
	<p>Drywall (2 x 12,5 mm) water-resistant</p> <p>Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.</p>	