




Product	PLUS 90° angle handrail 400 x 475 mm
Item number	RT115000
Colour	White
Product description	<p>VVS:777567100 NRF:6311217 RSK:8980564 EAN:5708590146270 HMI: 25432 NBS:N13:436</p> <p>PLUS handrails are high-quality products and they can be combined in countless ways and they provide the final touch to furnishing a functional and flexible bathroom. A reliable solution with many different options, which can easily lay the grounds for increased independence.</p> <p>PLUS handrail, angle 90° - left, diameter 33 mm, A: 400 mm x B: 475 mm, for fixed mounting. The projection of 50 mm from the wall makes it easy to take hold of the rail. Inkl. wall rosette, which covers the fixings. Material: Powder-coated aluminium and plastic. Excl. mounting kit.</p>
Product capacity	<p>Maximum load: 235 kg. When the handrail is loaded with 235 kg, each wall fastener is loaded with 56 kg. <i>Handrails are tested with a 1.5 safety factor in accordance with the requirements in ISO 17966:2016.</i></p>
Materials	<p>Basic material: Aluminium</p> <p>Surface material: Polyester lacquer</p> <p>Cover cap: Cycoloy plastic</p> <p>Strap: Nylon (PA)</p>
Ergonomy	<p>The 33 mm diameter enables the rail to be held comfortably and firmly. The projection of 50 mm from the wall makes it easy to take hold of the rail.</p>
Warranty	<p>Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.</p>





PRESSALIT®











Product	PLUS 90° angle handrail 400 x 475 mm
Item number	RT115000
Cleaning	<p>Handrails ALU.</p> <p>The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p>DISINFECTANTS: Clinimax Difficil-S Erisan OXY+</p> <p>NON-DISINFECTANTS: Suma Star free D1 Taski 100 Taski 200</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p> <p>DECALCIFICATION OF ALUMINUM PARTS: Pressalit recommends that chalky deposits be removed from wall tracks and other aluminum parts using a solution of three parts 30% acetic acid to seven parts tap water. When the aluminum parts have been washed down with this solution, the parts must be wiped over with a damp cloth wrung out in clear water.</p>
Declaration of conformity	<p>CE UK MDR This product is in compliance with all relevant requirements of: - Regulation (EU) 2017/745 on medical devices.</p> <p>For the UK: - Medical Device Regulation (MDR) 2002 on medical devices.</p>



PRESSALIT®

Product	PLUS 90° angle handrail 400 x 475 mm
Item number	RT115000

Installation in different wall types

	<p>Concrete >B25</p> <p>V8617 - Mounting kit, 12 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p> 
	<p>Solid Brick >= Mz12</p> <p>V8617 - Mounting kit, 12 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p> 
	<p>Solid Sand Lime Brick >= Hlz12</p> <p>V8617 - Mounting kit, 12 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p> 
	<p>Aerated Concrete P4</p> <p>V8667 - Mounting kit, 12 bolts M5 x 50 - plugs FTP K 6. To be ordered separately.</p> 
	<p>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</p> <p>V8617 - Mounting kit, 12 screws Ø5 x 50 - plugs SX8. NB! Plugs are not needed. To be ordered separately.</p> 



PRESSALIT®

Product Item number	PLUS 90° angle handrail 400 x 475 mm RT115000
	<p>Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood</p> <p>Wall fasteners (12 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.</p>
	<p>Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (2 mm)</p> <p>Wall fasteners (12 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.</p>
	<p>Drywall (2 x 12,5 mm) water-resistant</p> <p>Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.</p>

pressalit.com

Pressalit A/S
 Pressalitvej 1
 DK-8680 Ry
 Tel.: +45 8788 8788
 Fax: +45 8788 8789
 E-mail: pressalit@pressalit.com

PRESSALIT®